



Click [here](#) for the 3D model.

General Information

| | |
|-------------|--|
| Series | MR |
| Type | Current |
| Style | Round - Toroidal |
| Description | Zero-Phase Current Transformers |
| Features | High Sensitivity, Compact |
| Lead | 2 Pin |
| RoHS | Yes |
| REACH | Yes |
| Notes | Measurement Conditions: f=60Hz, R=1000 Ohms, I _o =15 mAmps |

Dimensions

| | |
|----|------------|
| D | 6mm MIN |
| H | 6.7mm MAX |
| D2 | 17.5mm MAX |
| D3 | 19mm MAX |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Tray |
| Packaging Quantity | 1200 |
| Typical Component Weight | 2.3 g |

Specifications

| | |
|-------------------|---|
| Temperature Range | -20/+80°C |
| Voltage DC | 12.5 mV MIN (Output) |
| Current | 15 Amps |
| ESR | 30 Ohms |
| Miscellaneous | Overinput characteristics (After DC5A input) = 10% MAX. |