



Click [here](#) for the 3D model.

Dimensions	
D	30mm +/-0.5mm
L	35mm +/-1mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	100

General Information	
Series	PEH534
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No
Typical Component Weight	34 g
Notes	Add 0.5mm To D And 1mm To L For Sleving.
Shelf Life	208 Weeks

Specifications	
Capacitance	470 uF
Tolerance	20%
Voltage DC	250 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	3000 Hrs (Rated Voltage And Ripple Current At 105C), 4000 Hrs (Rated Voltage At 105C)
ESR	240 mOhms (100Hz 20C), 110 mOhms (100kHz 20C)
Ripple Current	1.3 Amps (100Hz 105C), 10.1 Amps (20kHz 40C)
Leakage Current	353 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.