



Click [here](#) for the 3D model.

Dimensions	
L	5mm NOM
W	4.8mm NOM
T	1.7mm NOM

Packaging Specifications	
Packaging	T&R
Packaging Quantity	2000
Typical Component Weight	100 mg

General Information	
Series	PL
Type	Proximity
Style	SMD
Description	Sensor without Lens
Features	Detection Up To 2 Meters
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	b3250cc9-9746-4ec7-bd8a-a484c87e9021
Qualifications	REACH
MSL	3
Field of View	Horizontal & Vertical +/- 60 degrees

Specifications	
Temperature Range	-40/+70°C
Power Supply Voltage	2 -15 VDC
Miscellaneous	0.3 - 0.9 mV MAX (Source Voltage). Warm Up Time: 30 Sec (MAX).