



Click [here](#) for the 3D model.

Dimensions

D	7mm MAX
L	8mm MAX
S	4mm NOM
LL	3.5mm +1/-0.5mm
F	0.32mm NOM

Packaging Specifications

Typical Component Weight	710 mg
Packaging	Bulk
Packaging Quantity	3750

General Information

Series	SBC2
Style	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Core	Ferrite
Miscellaneous	Soft Lead Terminal

Specifications

Inductance	22 uH
Inductance Tolerance	20%
Temperature Range	-20/+105°C
Shielded	No
Current	1.3 Amps
DC Resistance	0.11 Ohms