


R75PR410050H3J

Aliases (75PR410050H3J)

R75H, Film, Metallized Polypropylene, Automotive Grade, 1 uF, 5%, 630 VDC, 105°C, 27.5mm



Click [here](#) for the 3D model.

Dimensions	
L	32mm +0.3/-0.7mm
H	22mm +0.1/-0.7mm
T	13mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	288

General Information	
Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	10.6 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Specifications	
Capacitance	1 uF
Capacitance Tolerance	5%
Voltage AC	250 VAC
Voltage DC	630 VDC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	180 V/us
ESR	23.9 mOhms (100kHz)
Ripple Current	9.3 Amps (100kHz 90C), 180 Amps (Peak)
Inductance	18 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.