

## R75RR322050L4J

Aliases (75RR322050L4J)

R75, Film, Metallized Polypropylene, General Purpose, 0.22 uF, 5%, 1250 VDC, 85°C, 27.5mm



Click [here](#) for the 3D model.

### Dimensions

L	32mm +0.3/-0.7mm
H	15mm +0.1/-0.7mm
T	24mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.4mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	144

### General Information

Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	12.1 g
Miscellaneous	Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C.

### Specifications

Capacitance	0.22 uF
Capacitance Tolerance	5%
Voltage AC	600 VAC
Voltage DC	1250 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	750 V/us
ESR	5.064 mOhms (100kHz)
Ripple Current	12.06 Amps (100kHz 85C), 165 Amps (Peak)
Inductance	18 nH