



#### General Information

Series	SS17HB
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530 or equivalent.

#### Dimensions

L	20mm MAX
T	17.85mm MAX
H	13.8mm MAX
LL	2.5mm +/-0.5mm
S	16mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.4mm
F	0.7mm +/-0.1mm

#### Specifications

Voltage AC	250 VAC
Inductance	2 mH
Rated Current	1.3 A
Temperature Range	-25/+120°C
DC Resistance	0.18 Ohms

#### Packaging Specifications

Typical Component Weight	6.2 g
--------------------------	-------