



#### General Information

Series	SS20H
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

#### Dimensions

L	22mm MAX
T	22mm MAX
H	18.5mm MAX
LL	3.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
F	0.8mm NOM

#### Specifications

Voltage AC	250 VAC
Inductance	1.8 mH
Rated Current	2 A
Temperature Range	-25/+120°C
DC Resistance	0.11 Ohms

#### Packaging Specifications

Typical Component Weight	12 g
--------------------------	------