



Click [here](#) for the 3D model.

Dimensions

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm NOM
Wire Size	0.35mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	10 g

General Information

Series	SSHB10HS
Style	Through-Hole
RoHS	Yes
Notes	Marking: 11 Lot No.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC, 320 VAC (IEC60664-1)
Inductance	4.3 mH (10 kHz)
Current	1.1 A
Temperature Range	-40/+130°C
DC Resistance	0.35 Ohms (Per Line)