



Click [here](#) for the 3D model.

General Information

| | |
|---------------|---------------------------------|
| Series | SSRH7H-M |
| Style | Through-Hole Bobbin |
| RoHS | Yes |
| Notes | M04 Lot No. |
| Miscellaneous | Temperature Rise Maximum: 55 K. |
| Core | Mn-Zn Ferrite |

Dimensions

| | |
|-----------|----------------|
| L | 18mm MAX |
| T | 14.5mm MAX |
| H | 12mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm NOM |
| S1 | 10mm NOM |
| Wire Size | 0.7mm |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Tray |
| Packaging Quantity | 600 |
| Typical Component Weight | 5.2 g |

Specifications

| | |
|-------------------|----------------------|
| Voltage AC | 250 VAC |
| Inductance | 59.6 mH (10 kHz) |
| Current | 400 mA |
| Temperature Range | -40/+120°C |
| DC Resistance | 2.02 Ohms (Per Line) |