



Click [here](#) for the 3D model.

#### General Information

Series	SSRH7H-M
Style	Through-Hole Bobbin
RoHS	Yes
Notes	M07 Lot No.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	18mm MAX
T	14.5mm MAX
H	12mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
S1	10mm NOM
Wire Size	0.7mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	5.2 g

#### Specifications

Voltage AC	250 VAC
Inductance	19.6 mH (10 kHz)
Current	700 mA
Temperature Range	-40/+120°C
DC Resistance	0.71 Ohms (Per Line)