



Click [here](#) for the 3D model.

#### General Information

Series	SSRH7HS-M
Style	Through-Hole Bobbin
RoHS	Yes
Notes	M10 Lot No.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	18mm MAX
T	14.5mm MAX
H	12mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
S1	10mm NOM
Wire Size	0.7mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	5.1 g

#### Specifications

Voltage AC	250 VAC
Inductance	8.4 mH
Current	1 A
Temperature Range	-40/+120°C
DC Resistance	0.32 Ohms (Per Line)