


## SBC4-101-102

Aliases (UPIN4101102000)

KEMET, SBC4, Ferrite, 10%, 100 uH, 9mm, 5.5mm



Click [here](#) for the 3D model.

### Dimensions

D	9mm MAX
L	12mm MAX
S	5.5mm NOM
F	0.32mm NOM

### Packaging Specifications

Typical Component Weight	2.012 g
Packaging	Bulk
Packaging Quantity	3000

### General Information

Series	SBC4
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

### Specifications

Inductance	100 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	1 Amps
DC Resistance	0.26 Ohms