



Click [here](#) for the 3D model.

#### General Information

|               |                                 |
|---------------|---------------------------------|
| Series        | SSHB21H                         |
| Style         | Through-Hole                    |
| RoHS          | Yes                             |
| Notes         | Marking: R10 Lot No.            |
| Miscellaneous | Temperature Rise Maximum: 65 K. |
| Core          | Mn-Zn Ferrite                   |

#### Dimensions

|           |                |
|-----------|----------------|
| L         | 26mm MAX       |
| T         | 23mm MAX       |
| H         | 15.5mm MAX     |
| LL        | 3.5mm +/-0.5mm |
| S         | 21mm +/-0.5mm  |
| S1        | 15mm NOM       |
| Wire Size | 0.32mm         |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Packaging                | Tray |
| Packaging Quantity       | 360  |
| Typical Component Weight | 14 g |

#### Specifications

|                   |                               |
|-------------------|-------------------------------|
| Voltage AC        | 250 VAC, 320 VAC (IEC60664-1) |
| Inductance        | 37.7 mH                       |
| Current           | 1A                            |
| Temperature Range | -40/+120°C                    |
| DC Resistance     | 0.64 Ohms (Per Line)          |