


T498A685M010ZGE2K7

Obsolete

Tantalum, MnO₂ Tantalum, High Temperature, 6.8 uF, 20%, 10 VDC, SMD, Molded, High Temperature, N/A, 2.7 Ohms, 3216, 1.8mm



Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm
K	1.3mm TYP

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	2000

General Information

Dielectric	MnO ₂ Tantalum
Style	SMD Chip
Description	SMD, Molded, High Temperature
Features	High Temperature
RoHS	Yes
Termination	Gold
AEC-Q200	No
Notes	Old Part Number [Obsolete] Was B45198P2685M109.

Specifications

Capacitance	6.8 uF
Capacitance Tolerance	20%
Voltage DC	10 VDC (85C), 7.97 VDC (125C), 6.7 VDC (150C)
Temperature Range	-55/+150°C
Rated Temperature	85°C
Dissipation Factor	4.5%
Failure Rate	N/A
ESR	2.7 Ohms (100kHz)
Leakage Current	0.7 uA