


## B45196L2335M106

Aliases (T495A335M010ZTA5K57280)

Obsolete

Tantalum, MnO<sub>2</sub> Tantalum, 3.3 uF, 20%, 10 VDC, SMD, Molded, Automotive, 5.5 Ohms, 3216, 1.8mm



### General Information

Dielectric	MnO <sub>2</sub> Tantalum
Style	SMD Chip
Description	SMD, Molded, Automotive
Features	Automotive
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	AEC-Q200.
Notes	Obsolete.

### Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm
K	1.3mm TYP

### Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	9000

### Specifications

Capacitance	3.3 uF
Capacitance Tolerance	20%
Voltage DC	10 VDC (85C), 6.7 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6%
Failure Rate	N/A
ESR	5.5 Ohms (100kHz)
Ripple Current	91.3 mAmps (25C), 82.2 mAmps (85C), 36.5 mAmps (125C)
Leakage Current	0.5 uA