



### General Information

Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, Automotive
Features	Automotive
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	AEC-Q200.
Notes	Obsolete.

### Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1.8mm TYP

### Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	750

### Specifications

Capacitance	22 uF
Capacitance Tolerance	10%
Voltage DC	20 VDC (85C), 13.4 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6%
Failure Rate	N/A
ESR	1.4 Ohms (100kHz)
Ripple Current	110.6 mAmps (25C), 99.5 mAmps (85C), 44.2 mAmps (125C)
Leakage Current	4.4 uA