


T495M107K006ZTE500

Obsolete

Tantalum, MnO₂ Tantalum, 100 uF, 10%, 6.3 VDC, SMD, Molded, Low Profile, Low ESR, Surge Robust, 500 mOhms, 3528, 1.5mm



Dimensions

Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.5mm MAX
S	0.8mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1.3mm TYP

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	2500

General Information

Dielectric	MnO ₂ Tantalum
Style	SMD Chip
Description	SMD, Molded, Low Profile, Low ESR, Surge Robust
Features	Low Profile, Low ESR, Surge Robust
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Obsolete. Old Part Number [Obsolete] Was B45006Y1079K507.

Specifications

Capacitance	100 uF
Capacitance Tolerance	10%
Voltage DC	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	20%
Failure Rate	N/A
ESR	0.5 Ohms (100kHz)
Ripple Current	390 mAmps (25C), 351 mAmps (85C), 156 mAmps (125C)
Leakage Current	6.3 uA