


T495T106M006ZTE1K2

Obsolete

Tantalum, MnO₂ Tantalum, 10 uF, 20%, 6.3 VDC, SMD, Molded, Low Profile, Low ESR, Surge Robust, 1.2 Ohms, 3528, 1.2mm



General Information	
Dielectric	MnO ₂ Tantalum
Style	SMD Chip
Description	SMD, Molded, Low Profile, Low ESR, Surge Robust
Features	Low Profile, Low ESR, Surge Robust
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Obsolete. Old Part Number [Obsolete] Was B45190R1106M209.

Specifications	
Capacitance	10 uF
Capacitance Tolerance	20%
Voltage DC	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6%
Failure Rate	N/A
ESR	1.2 Ohms (100kHz)
Ripple Current	250 mAmps (25C), 225 mAmps (85C), 100 mAmps (125C)
Leakage Current	0.6 uA

Dimensions	
Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.2mm MAX
S	0.8mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1mm TYP

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	2500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.