



Click [here](#) for the 3D model.

#### General Information

Series	TCA Indust COG HT260C
Description	Commercial, High Temperature
Features	High Temperature
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
Termination	Lead (SnPb)
AEC-Q200	No

#### Dimensions

L	10.16mm MAX
W	3.81mm MAX
T	3.81mm MAX
LL	31.75mm MIN
F	0.635mm +/-0.051mm

#### Packaging Specifications

Packaging	Waffle, Tray
Packaging Quantity	25

#### Specifications

Capacitance	4,700 pF
Tolerance	5%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+260°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1kHz 1.0Vrms
Dissipation Factor	0.15% 1 kHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.