



Click [here](#) for the 3D model.

General Information	
Series	QGC
Type	Gas Detection
Style	TO39
Description	Analog output gas sensor
Features	Fast, Wide Operating Frequency Range, Analog Output, Integrated op amp
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	9074c9fd-06c9-4bc8-bb2f-04f9793401ba
Qualifications	REACH

Specifications	
Temperature Range	-40/+85°C
Power Supply Voltage	2.7 - 5.0 V
Microphonics	S(vib) ~1 μV/sqrt(Hz) (at 10 Hz)
Noise	Mean 40 μV sqrt(Hz)
D*	1.5 x 10 ⁸ cm sqrt(Hz)/ W
Time Constant	10ms
Element Size	1000um x 1000um
Filter Aperture	0.7mm x 0.325mm
Filter	Detection: Exhaust, Environmental
Responsivity	100,000 V/W

Dimensions	
L	9.15mm +/-0.05mm
W	9.15mm +/-0.05mm
H	19.5mm +/-0.75mm
T	6.05mm NOM

Packaging Specifications	
Packaging	Bulk
Typical Component Weight	1.15 g