


T499A155M020ZTE5K2

Obsolete

B45196T, Tantalum, MnO₂ Tantalum, High Temperature, 1.5 uF, 20%, 20 VDC, SMD, Molded, High Temperature, N/A, 5.2 Ohms, 3216, 1.8mm



General Information	
Series	B45196T
Dielectric	MnO ₂ Tantalum
Style	SMD Chip
Description	SMD, Molded, High Temperature
Features	High Temperature, Automotive
RoHS	Yes
Termination	Tin
AEC-Q200	No

Specifications	
Capacitance	1.5 uF
Capacitance Tolerance	20%
Voltage DC	20 VDC (85C), 15.56 VDC (125C), 10 VDC (175C)
Temperature Range	-55/+175°C
Rated Temperature	85°C
Dissipation Factor	4.5%
Failure Rate	N/A
ESR	5.2 Ohms (100kHz)
Ripple Current	120.1 mAmps (25C), 108.1 mAmps (85C), 48 mAmps (125C)
Leakage Current	0.5 uA

Dimensions	
Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	2000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.