



Click [here](#) for the 3D model.

#### General Information

Series	VCR Indust COG HVHT200C
Style	Radial
Description	Commercial, High Temperature, HighVoltage
Features	Commercial
RoHS	With Exemptions
REACH	SVHC (Pb – CAS 7439-92-1)
SCIP Number	d1f8aba3-2564-4904-a1cf-714f e85ef1ab
Termination	Gold
Lead	Wire Leads
Testing and Reliability	Standard
AEC-Q200	No

#### Dimensions

L	13.97mm MAX
W	15.24mm MAX
T	9.52mm MAX
S	10.16mm +/-0.76mm
LL	31.75mm MIN
F	0.813mm +/-0.102mm

#### Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

#### Specifications

Capacitance	3,900 pF
Tolerance	10%
Voltage DC	4000 VDC
Temperature Range	-55/ +200°C
Temp. Coefficient	COG
Dissipation Factor	0.15% 1 kHz 1.0Vrms
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.