


VU-215F3

Aliases (UNFVU215F3XXXX)

Obsolete

KEMET, VU, EMI/RFI Filters, Noise Suppression, 250 VAC, 15 A



Click [here](#) for the 3D model.

Dimensions	
D	45mm NOM
L	40mm NOM
L1	12mm NOM
L2	12mm NOM

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	60
Typical Component Weight	105 g

General Information	
Series	VU
Style	Metal Cylinder
Description	Noise Filters
RoHS	With Exemptions
Qualifications	UL, CSA
Notes	Last time buy due: May 31, 2024.
Miscellaneous	40 K Self-Temperature Rise Max.
Terminal Type	Faston

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	15 A (AC/DC)
Ripple Current	15 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	1 mA MAX (250 V 60 Hz)
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.