



Click [here](#) for the 3D model.

General Information

Series	QGC
Type	Gas Detection
Style	TO39
Description	Analog output gas sensor
Features	Fast, Wide Operating Frequency Range, Analog Output, Integrated op amp
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	9074c9fd-06c9-4bc8-bb2f-04f9793401ba
Qualifications	REACH

Specifications

Temperature Range	-40/+85°C
Power Supply Voltage	2.7 - 8.0 V
Microphonics	S(vib) ~2 µV/sqrt(Hz) (at 10 Hz)
Noise	Mean 70 µV sqrt(Hz)
D*	3.5 x 10 ⁸ cm sqrt(Hz)/ W
Time Constant	12ms
Element Size	1000um x 1000um
Filter Aperture	2.5 mm diameter
Filter	Detection: CO (Narrow)
Responsivity	150,000 V/W

Dimensions

L	9.13mm +/-0.06mm
W	9.13mm +/-0.06mm
H	17.65mm +/-1mm
T	4.15mm NOM

Packaging Specifications

Packaging	Bulk
Typical Component Weight	930 mg