



Click [here](#) for the 3D model.

General Information

Supplier	KEMET
Series	VP
Type	Varistors
Style	SMD Molded
Description	Surface Mount Varistors
Features	Plastic Encapsulated
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	UL
AEC-Q200	No

Dimensions

Chip Size	3225
L	8mm +/-0.5mm
W	6.3mm +/-0.4mm
H	3.4mm +/-0.3mm
F	3mm +/-0.3mm
B	1.5mm +/-0.3mm
K	1.7mm +/-0.3mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	1500

Specifications

Voltage DC	85 VDC (25C)
Voltage AC	60 VAC
Temperature Range	-40/+85°C
Storage Temperature Range	-40/+125°C
Varistor Voltage	100 VDC at 1 mA
Clamping Voltage	165 V
Clamping Current	5 A (8/20 us MAX)
Surge Current	400 A (8/20 us MAX)
Energy	3 J (10/1000 us MAX)
Power	0.1 W (MAX)
Capacitance	330 pF (1kHz)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.