

High Temperature 150°C, X8G Dielectric, 10 – 250 VDC (Commercial & Automotive Grade)



Overview

KEMET's X8G Class I dielectric features a 150°C maximum operating temperature, offering the latest in high temperature dielectric technology and reliability for extreme temperature applications and under the hood applications. X8G exhibits no change in capacitance with respect to voltage and boasts a minimal change in capacitance with reference to ambient temperature. It is a suitable replacement for higher capacitance and larger footprint devices that fail to offer capacitance stability. Capacitance change is limited to $\pm 30\text{ppm}/^\circ\text{C}$ from -55°C to $+150^\circ\text{C}$.

Driven by the demand for a more robust and reliable component, X8G dielectric capacitors were developed for critical applications where reliability and capacitance

stability at higher operating temperatures are a concern. These capacitors are widely used in automotive for under the hood and harsh environment as well as general high temperature applications.


In addition to commercial grade, automotive grade devices are available and meet Automotive Electronics Council's AEC-Q200 qualification requirements. Also available with flexible termination technology which inhibits the transfer of board stress to the rigid ceramic body, therefore mitigating flex cracks which can result in low IR or short circuit failures.

Benefits

- -55°C to $+150^\circ\text{C}$ operating temperature range
- Lead (Pb)-Free, RoHS and REACH compliant
- EIA 0402, 0603, 0805, 1206, 1210, 1812 & 2220 case sizes
- DC voltage ratings of 10V, 16V, 25V, 50V, 100V, 200V & 250V
- Capacitance offerings ranging from 0.5pF to 0.47 μF
- Available capacitance tolerances of $\pm 0.10\text{pF}$, $\pm 0.25\text{pF}$, $\pm 0.5\text{pF}$, $\pm 1\%$, $\pm 2\%$, $\pm 5\%$, $\pm 10\%$ & $\pm 20\%$,
- Extremely low ESR and ESL
- High thermal stability
- High ripple current capability
- No capacitance change with respect to applied rated DC voltage
- Non-polar device, minimizing installation concerns
- Commercial and Automotive (AEC-Q200) grades available
- 100% pure matte tin-plated termination finish that allowing for excellent solderability.
- Flexible Termination option available

Applications

- Decoupling
- Bypass
- Filtering
- Under the hood
- Transient voltage suppression
- Safety relevant circuits



Ordering Information

| C | 1210 | C | 184 | K | 3 | T | A | C | AUTO |
|---------|--|---|--|--|---|------------|---------------------|---|---|
| Ceramic | Case Size (L" x W") | Specification/ Series ¹ | Capacitance Code (pF) | Capacitance Tolerance | Rated Voltage (VDC) | Dielectric | Failure Rate/Design | Termination Finish ² | Packaging/ Grade (C-Spec) |
| | 0402 0603 0805 1206 1210 1812 2220 | C = Standard X = Flexible Termination | Two significant digits and number of zeros | B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20% | 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250 | T = X8G | A = N/A | C = 100% Matte Sn L = SnPb (5% Pb minimum) | See "Packaging C-Spec Ordering Options Table" |

¹ The flexible termination option is not available on EIA 0402 case size product. "C" must be used in the 6th character position when ordering this case size.

² Additional termination finish options may be available. Contact KEMET for details.

³ SnPb termination finish option is not available on automotive grade product.

Packaging C-Spec Ordering Options Table

| Packaging Type | Packaging/Grade Ordering Code (C-Spec) |
|---|---|
| Commercial Grade¹ | |
| Bulk Bag | Not Required (Blank) |
| 7" Reel/Unmarked | TU |
| 13" Reel/Unmarked | 7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes) |
| 7" Reel/Unmarked/2 mm pitch ² | 7081 |
| 13" Reel/Unmarked/2 mm pitch ² | 7082 |
| Automotive Grade³ | |
| 7" Reel | AUTO |
| 13" Reel/Unmarked | AUTO7411 (EIA 0603 and smaller case sizes) AUTO7210 (EIA 0805 and larger case sizes) |
| 7" Reel/Unmarked/2 mm pitch ² | 3190 |
| 13" Reel/Unmarked/2 mm pitch ² | 3191 |

¹ Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

¹ The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked.

² The 2 mm pitch option allows for double the packaging quantity of capacitors on a given reel size. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".

³ Reeling tape options (Paper or Plastic) are dependent on capacitor case size (L" x W") and thickness dimension. See "Chip Thickness/Tape & Reel Packaging Quantities" and "Tape & Reel Packaging Information".

³ For additional information regarding "AUTO" C-Spec options, see "Automotive C-Spec Information".

³ All Automotive packaging C-Specs listed exclude the option to laser mark components. Please contact KEMET if you require a laser marked option. For more information see "Capacitor Marking".

Automotive C-Spec Information

KEMET automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. These products are supported by a Product Change Notification (PCN) and Production Part Approval Process warrant (PPAP).

Automotive products offered through our distribution channel have been assigned an inclusive ordering code C-Spec, "AUTO." This C-Spec was developed in order to better serve small and medium-sized companies that prefer an automotive grade component without the requirement to submit a customer Source Controlled Drawing (SCD) or specification for review by a KEMET engineering specialist. This C-Spec is therefore not intended for use by KEMET OEM automotive customers and are not granted the same "privileges" as other automotive C-Specs. Customer PCN approval and PPAP request levels are limited (see details below.)

Product Change Notification (PCN)

The KEMET product change notification system is used to communicate primarily the following types of changes:

- Product/process changes that affect product form, fit, function, and/or reliability
- Changes in manufacturing site
- Product obsolescence

| KEMET Automotive C-Spec | Customer Notification Due To: | | Days Prior To Implementation |
|-----------------------------|----------------------------------|---------------|------------------------------|
| | Process/Product change | Obsolescence* | |
| KEMET assigned ¹ | Yes (with approval and sign off) | Yes | 180 days minimum |
| AUTO | Yes (without approval) | Yes | 90 days minimum |

¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

Production Part Approval Process (PPAP)

The purpose of the Production Part Approval Process is:


- To ensure that supplier can meet the manufacturability and quality requirements for the purchased parts.
- To provide the evidence that all customer engineering design records and specification requirements are properly understood and fulfilled by the manufacturing organization.
- To demonstrate that the established manufacturing process has the potential to produce the part.

| KEMET Automotive C-Spec | PPAP Level | | | | |
|-----------------------------|------------|---|---|---|---|
| | 1 | 2 | 3 | 4 | 5 |
| KEMET assigned ¹ | ● | ● | ● | ● | ● |
| AUTO | | | ○ | | |

¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

- Part number specific PPAP available with customer information included.
- Product family PPAP only

Dimensions – Millimeters (Inches)



Standard Termination

| EIA Size Code | Metric Size Code | L Length | W Width | T Thickness | B Bandwidth | S Separation Minimum | Mounting Technique |
|---------------|------------------|-------------------------------|-------------------------------|---------------------------|-------------------------------|----------------------|------------------------------|
| 0402 | 1005 | 1.00 (0.040) ±0.05 (0.002) | 0.50 (0.020) ±0.05 (0.002) | See Table 2 for Thickness | 0.30 (0.012) ±0.10 (0.004) | 0.30 (0.012) | Solder Reflow Only |
| 0603 | 1608 | 1.60 (0.063) ±0.15 (0.006) | 0.80 (0.032) ±0.15 (0.006) | | 0.35 (0.014) ±0.15 (0.006) | 0.70 (0.028) | Solder Wave or Solder Reflow |
| 0805 | 2012 | 2.00 (0.079) ±0.20 (0.008) | 1.25 (0.049) ±0.20 (0.008) | | 0.50 (0.02) ±0.25 (0.010) | 0.75 (0.030) | |
| 1206 | 3216 | 3.20 (0.126) ±0.20 (0.008) | 1.60 (0.063) ±0.20 (0.008) | | 0.50 (0.02) ±0.25 (0.010) | N/A | Solder Reflow Only |
| 1210 | 3225 | 3.20 (0.126) ±0.20 (0.008) | 2.50 (0.098) ±0.20 (0.008) | | 0.50 (0.02) ±0.25 (0.010) | | |
| 1812 | 4532 | 4.50 (0.177) ±0.30 (0.012) | 3.20 (0.126) ±0.30 (0.012) | | 0.60 (0.024) ±0.35 (0.014) | | |
| 2220 | 5650 | 5.70 (0.224) ±0.40 (0.016) | 5.00 (0.197) ±0.40 (0.016) | | 0.60 (0.024) ±0.35 (0.014) | | |

Flexible Termination

| EIA Size Code | Metric Size Code | L Length | W Width | T Thickness | B Bandwidth | S Separation Minimum | Mounting Technique |
|---------------|------------------|-------------------------------|-------------------------------|---------------------------|-------------------------------|----------------------|------------------------------|
| 0603 | 1608 | 1.60 (0.063) ±0.17 (0.007) | 0.80 (0.032) ±0.15 (0.006) | See Table 2 for Thickness | 0.45 (0.018) ±0.15 (0.006) | 0.58 (0.023) | Solder Wave or Solder Reflow |
| 0805 | 2012 | 2.00 (0.079) ±0.30 (0.012) | 1.25 (0.049) ±0.30 (0.012) | | 0.50 (0.02) ±0.25 (0.010) | 0.75 (0.030) | |
| 1206 | 3216 | 3.30 (0.130) ±0.40 (0.016) | 1.60 (0.063) ±0.35(0.013) | | 0.60 (0.024) ±0.25 (0.010) | N/A | Solder Reflow Only |
| 1210 | 3225 | 3.30 (0.130) ±0.40 (0.016) | 2.60(0.102) ±0.30(0.012) | | 0.60 (0.024) ±0.25 (0.010) | | |
| 1812 | 4532 | 4.50 (0.178) ±0.40 (0.016) | 3.20 (0.126) ±0.30 (0.012) | | 0.70 (0.028) ±0.35 (0.014) | | |
| 2220 | 5650 | 5.90 (0.232) ±0.75 (0.030) | 5.00 (0.197) ±0.40 (0.016) | | 0.70 (0.028) ±0.35 (0.014) | | |

Qualification/Certification

Commercial grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance & Reliability.

Automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.

Environmental Compliance



Lead (Pb)-free, RoHS, and REACH compliant without exemptions (excluding SnPb termination finish option).

Table 1A – Standard Termination Capacitance Range/Selection Waterfall (0402 – 1206 Case Sizes)

| Capacitance | Cap Code | Case Size/Series | | | | C0402C | | | | | | | | C0603C | | | | | | | | C0805C | | | | | | | | C1206C | | | | | | | |
|----------------|------------|-----------------------|---|---|----|--|----|----|----|-----|-----|-----|----|--------|----|----|-----|-----|-----|----|----|--------|----|-----|-----|-----|----|----|----|--------|-----|-----|-----|--|--|--|--|
| | | Voltage Code | | | | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | | | | |
| | | Rated Voltage (VDC) | | | | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | | | | |
| | | Capacitance Tolerance | | | | Product Availability and Chip Thickness Codes See Table 2 for Chip Thickness Dimensions | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.50 & 0.75 pF | 508 & 758 | B | C | D | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 0.75 pF | 758 | B | C | D | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 1.0 - 9.1 pF* | 109 - 919* | B | C | D | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 10 pF | 100 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 11 pF | 110 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 12 pF | 120 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 13 pF | 130 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 15 pF | 150 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 16 pF | 160 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 18 pF | 180 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 20 pF | 200 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 22 pF | 220 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 24 pF | 240 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 27 pF | 270 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 30 pF | 300 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 33 pF | 330 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 36 pF | 360 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 39 pF | 390 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 43 pF | 430 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 47 pF | 470 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 51 pF | 510 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 56 pF | 560 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 62 pF | 620 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 68 pF | 680 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 75 pF | 750 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 82 pF | 820 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 91 pF | 910 | F | G | J | K | M | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EB | EB | EB | | | | | | | |
| 100 pF | 101 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 110 pF | 111 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 120 pF | 121 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 130 pF | 131 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 150 pF | 151 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 160 pF | 161 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 180 pF | 181 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 200 pF | 201 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 220 pF | 221 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 240 pF | 241 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 270 pF | 271 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 300 pF | 301 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 330 pF | 331 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 360 pF | 361 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 390 pF | 391 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 430 pF | 431 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 470 pF | 471 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DP | DP | | | | | | | | |
| 510 pF | 511 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 560 pF | 561 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 620 pF | 621 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 680 pF | 681 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 750 pF | 751 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 820 pF | 821 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DN | DN | | | | | | | | |
| 910 pF | 911 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DP | DP | | | | | | | | |
| 1,000 pF | 102 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CF | CF | CF | DN | DN | DN | DN | DN | DP | DP | | | | | | | | |
| 1,100 pF | 112 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CH | CH | CH | DN | DN | DN | DN | DN | DP | DP | | | | | | | | |
| 1,200 pF | 122 | F | G | J | K | M | BB | BB | BB | BB | BB | BB | BB | BB | BB | CF | CF | CF | CF | CH | CH | CH | DN | DN | DN | DN | DN | DP | DP | | | | | | | | |

**Table 1A – Standard Termination Capacitance Range/Selection Waterfall
 (0402 – 1206 Case Sizes) cont.**

| Capacitance | Cap Code | Case Size/Series | C0402C | | | | | | | | C0603C | | | | | | | | C0805C | | | | | | | | C1206C | | | | | | | | | |
|-------------|----------|-----------------------|--|----|----|----|-----|-----|-----|----|--------|----|----|-----|-----|-----|----|----|--------|----|-----|-----|-----|----|----|----|--------|-----|-----|-----|----|----|----|----|----|----|
| | | Voltage Code | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | | | | | | |
| | | Rated Voltage (VDC) | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | | | | | | |
| | | Capacitance Tolerance | Product Availability and Chip Thickness Codes See Table 2 for Chip Thickness Dimensions | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1,300 pF | 132 | | F | G | J | K | M | BB | BB | BB | BB | | | | | CF | CF | CF | CF | CF | CH | CH | DP | DP | DP | DP | DP | DN | DN | EB | EB | EB | EB | EC | EC | EC |
| 1,500 pF | 152 | | F | G | J | K | M | BB | BB | BB | BB | | | | | CF | CF | CF | CF | CF | CH | CH | DP | DP | DP | DP | DP | DN | DN | EB | EB | EB | EB | ED | ED | ED |
| 1,600 pF | 162 | | F | G | J | K | M | BB | BB | BB | | | | | | CF | CF | CF | CF | CF | CH | CH | DP | DP | DP | DP | DP | DN | DN | EB | EB | EB | EB | ED | ED | ED |
| 1,800 pF | 182 | | F | G | J | K | M | BB | BB | BB | | | | | | CF | CF | CF | CF | CF | CH | CH | DP | DP | DP | DP | DP | DN | DN | EB | EB | EB | EB | ED | ED | ED |
| 2,000 pF | 202 | | F | G | J | K | M | BB | BB | BB | | | | | | CF | CF | CF | CF | CF | CH | CH | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | ED | ED | ED |
| 2,200 pF | 222 | | F | G | J | K | M | BB | BB | BB | | | | | | CF | CF | CF | CF | CF | CH | CH | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EE | EE | ED |
| 2,400 pF | 242 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EC | EC | EC |
| 2,700 pF | 272 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DN | DN | EB | EB | EB | EB | EC | EC | EC |
| 3,000 pF | 302 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DN | DN | EC | EC | EC | EC | EC | EC | EB |
| 3,300 pF | 332 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DN | DN | EC | EC | EC | EC | EE | EB | EB |
| 3,600 pF | 362 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DP | DP | EC | EC | EC | EC | EE | EB | EB |
| 3,900 pF | 392 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DP | DP | EC | EC | EC | EC | EF | EB | EB |
| 4,300 pF | 432 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DP | DP | EC | EC | EC | EC | EC | EC | EB |
| 4,700 pF | 472 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | CF | | | DN | DN | DN | DN | DN | DP | DP | EC | EC | EC | EC | EC | EB | EB |
| 5,100 pF | 512 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | | | | DN | DN | DN | DN | DN | DP | DP | ED | ED | ED | ED | ED | EB | EB |
| 5,600 pF | 562 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | | | | DN | DN | DN | DN | DN | DP | DP | ED | ED | ED | ED | ED | EB | EB |
| 6,200 pF | 622 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | | | | DN | DN | DN | DN | DN | DG | DG | EB | EB | EB | EB | EB | EB | EB |
| 6,800 pF | 682 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | CF | | | | DN | DN | DN | DN | DN | DG | DG | EB | EB | EB | EB | EB | EB | EB |
| 7,500 pF | 752 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DN | DN | DG | DG | EB | EB | EB | EB | EB | EB | EB |
| 8,200 pF | 822 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DN | DN | DG | DG | EB | EB | EB | EB | EB | EC | EC |
| 9,100 pF | 912 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DN | DN | | | EB | EB | EB | EB | EB | EC | EC |
| 10,000 pF | 103 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DN | DP | | | EB | EB | EB | EB | EB | EC | EC |
| 12,000 pF | 123 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DN | DE | | | EB | EB | EB | EB | EB | ED | ED |
| 15,000 pF | 153 | | F | G | J | K | M | | | | | | | | | CF | CF | CF | | | | | DN | DN | DN | DP | DG | | | EB | EB | EB | EB | EB | EF | EF |
| 18,000 pF | 183 | | F | G | J | K | M | | | | | | | | | | | | | | | | DN | DN | DN | DP | | | | EB | EB | EB | EB | EB | EH | EH |
| 22,000 pF | 223 | | F | G | J | K | M | | | | | | | | | | | | | | | | DP | DP | DP | DF | | | | EB | EB | EB | EB | EC | EH | EH |
| 27,000 pF | 273 | | F | G | J | K | M | | | | | | | | | | | | | | | | DF | DF | DF | | | | | EB | EB | EB | EB | EE | | |
| 33,000 pF | 333 | | F | G | J | K | M | | | | | | | | | | | | | | | | DG | DG | DG | | | | | EB | EB | EB | EB | EE | | |
| 39,000 pF | 393 | | F | G | J | K | M | | | | | | | | | | | | | | | | DG | DG | DG | | | | | EC | EC | EC | EE | EH | | |
| 47,000 pF | 473 | | F | G | J | K | M | | | | | | | | | | | | | | | | DG | DG | DG | | | | | EC | EC | EC | EE | EH | | |
| 56,000 pF | 563 | | F | G | J | K | M | | | | | | | | | | | | | | | | | | | | | | | ED | ED | ED | EF | | | |
| 68,000 pF | 683 | | F | G | J | K | M | | | | | | | | | | | | | | | | | | | | | | | EF | EF | EF | EH | | | |
| 82,000 pF | 823 | | F | G | J | K | M | | | | | | | | | | | | | | | | | | | | | | | EH | EH | EH | EH | | | |
| 100,000 pF | 104 | | F | G | J | K | M | | | | | | | | | | | | | | | | | | | | | | | EH | EH | EH | | | | |
| Capacitance | Cap Code | Rated Voltage (VDC) | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | | | | | | |
| | | Voltage Code | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | | | | | | |
| | | Case Size/Series | C0402C | | | | | | | | C0603C | | | | | | | | C0805C | | | | | | | | C1206C | | | | | | | | | |

Table 1B – Standard Termination Capacitance Range/Selection Waterfall (1210 – 2220 Case Sizes) cont.

| Capacitance | Cap Code | Case Size/Series | | | | | C1210C | | | | | | | C1812C | | | | C2220C | | | | |
|-------------|----------|-----------------------|--|---|---|---|--|----|----|----|-----|-----|-----|--------|-----|-----|-----|--------|-----|-----|----|----|
| | | Voltage Code | | | | | 8 | 4 | 3 | 5 | 1 | 2 | A | 5 | 1 | 2 | A | 5 | 1 | 2 | | |
| | | Rated Voltage (VDC) | | | | | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 50 | 100 | 200 | 250 | 50 | 100 | 200 | | |
| | | Capacitance Tolerance | | | | | Product Availability and Chip Thickness Codes See Table 2 for Chip Thickness Dimensions | | | | | | | | | | | | | | | |
| 1,600 pF | 162 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FE | FE | GB | GB | GB | GB | | | |
| 1,800 pF | 182 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FE | FE | GB | GB | GB | GB | | | |
| 2,000 pF | 202 | | | F | G | J | K | M | FB | FB | FB | FB | FC | FE | FE | GB | GB | GB | GB | | | |
| 2,200 pF | 222 | | | F | G | J | K | M | FB | FB | FB | FB | FC | FG | FG | GB | GB | GB | GB | | | |
| 2,400 pF | 242 | | | F | G | J | K | M | FB | FB | FB | FB | FC | FC | FC | | | | | | | |
| 2,700 pF | 272 | | | F | G | J | K | M | FB | FB | FB | FB | FC | FC | FC | GB | GB | GB | GB | | | |
| 3,000 pF | 302 | | | F | G | J | K | M | FB | FB | FB | FB | FC | FF | FF | | | | | | | |
| 3,300 pF | 332 | | | F | G | J | K | M | FB | FB | FB | FB | FF | FF | FF | GB | GB | GB | GB | | | |
| 3,600 pF | 362 | | | F | G | J | K | M | FB | FB | FB | FB | FF | FF | FF | | | | | | | |
| 3,900 pF | 392 | | | F | G | J | K | M | FB | FB | FB | FB | FF | FF | FF | GB | GB | GB | GB | | | |
| 4,300 pF | 432 | | | F | G | J | K | M | FB | FB | FB | FB | FF | FF | FF | | | | | | | |
| 4,700 pF | 472 | | | F | G | J | K | M | FF | FF | FF | FF | FG | FG | FG | GB | GB | GD | GD | | | |
| 5,100 pF | 512 | | | F | G | J | K | M | FB | FB | FB | FB | FG | FG | FG | | | | | | | |
| 5,600 pF | 562 | | | F | G | J | K | M | FB | FB | FB | FB | FG | FG | FG | GB | GB | GH | GH | | | |
| 6,200 pF | 622 | | | F | G | J | K | M | FB | FB | FB | FB | FG | FB | FB | | | | | | | |
| 6,800 pF | 682 | | | F | G | J | K | M | FB | FB | FB | FB | FG | FB | FB | GB | GB | GJ | GJ | JE | JE | JB |
| 7,500 pF | 752 | | | F | G | J | K | M | FC | FC | FC | FC | FC | FB | FB | | | | | | | |
| 8,200 pF | 822 | | | F | G | J | K | M | FC | FC | FC | FC | FC | FB | FB | GB | GH | GB | GB | JE | JE | JB |
| 9,100 pF | 912 | | | F | G | J | K | M | FE | FE | FE | FE | FE | FB | FB | | | | | | | |
| 10,000 pF | 103 | | | F | G | J | K | M | FF | FF | FF | FF | FF | FB | FB | GB | GH | GB | GB | JE | JE | JB |
| 12,000 pF | 123 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FB | FB | GB | GG | GB | GB | JE | JE | JB |
| 15,000 pF | 153 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FC | FC | GB | GB | GB | GB | JE | JE | JB |
| 18,000 pF | 183 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FC | FC | GB | GB | GB | GB | JE | JE | JB |
| 22,000 pF | 223 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FF | FF | GB | GB | GB | GB | JE | JB | JB |
| 27,000 pF | 273 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FG | FG | GB | GB | GB | GB | JE | JB | JB |
| 33,000 pF | 333 | | | F | G | J | K | M | FB | FB | FB | FB | FB | FH | FH | GB | GB | GB | GB | JB | JB | JB |
| 39,000 pF | 393 | | | F | G | J | K | M | FB | FB | FB | FB | FE | FH | FH | GB | GB | GB | GB | JB | JB | JB |
| 47,000 pF | 473 | | | F | G | J | K | M | FB | FB | FB | FB | FE | FJ | FJ | GB | GB | GD | GD | JB | JB | JB |
| 56,000 pF | 563 | | | F | G | J | K | M | FB | FB | FB | FB | FF | | | GB | GB | GD | GD | JB | JB | JB |
| 68,000 pF | 683 | | | F | G | J | K | M | FB | FB | FB | FC | FG | | | GB | GB | GK | GK | JB | JB | JB |
| 82,000 pF | 823 | | | F | G | J | K | M | FC | FC | FC | FF | FH | | | GB | GB | GM | GM | JB | JB | JB |
| 100,000 pF | 104 | | | F | G | J | K | M | FE | FE | FE | FG | FM | | | GB | GD | GM | GM | JB | JB | JD |
| 120,000 pF | 124 | | | F | G | J | K | M | FG | FG | FG | FH | | | | GB | GH | | | JB | JB | JD |
| 150,000 pF | 154 | | | F | G | J | K | M | FH | FH | FH | FM | | | | GD | GN | | | JB | JB | JG |
| 180,000 pF | 184 | | | F | G | J | K | M | FJ | FJ | FJ | | | | | GH | | | | JB | JD | JG |
| 220,000 pF | 224 | | | F | G | J | K | M | | | | | | | | GK | | | | JB | JD | JL |
| 270,000 pF | 274 | | | F | G | J | K | M | | | | | | | | | | | | JB | JF | |
| 330,000 pF | 334 | | | F | G | J | K | M | | | | | | | | | | | | JD | JG | |
| 390,000 pF | 394 | | | F | G | J | K | M | | | | | | | | | | | | JG | | |
| 470,000 pF | 474 | | | F | G | J | K | M | | | | | | | | | | | | JG | | |
| Capacitance | Cap Code | Rated Voltage (VDC) | | | | | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 50 | 100 | 200 | 250 | 50 | 100 | 200 | | |
| | | Voltage Code | | | | | 8 | 4 | 3 | 5 | 1 | 2 | A | 5 | 1 | 2 | A | 5 | 1 | 2 | | |
| | | Case Size/Series | | | | | C1210C | | | | | | | C1812C | | | | C2220C | | | | |



Table 1C – Flexible Termination Capacitance Range/Selection Waterfall (0603 – 1206 Case Sizes) cont.

| Capacitance | Cap Code | Case Size/Series | | C0603C | | | | | | | | C0805C | | | | | | | | C1206C | | | | | | | | | | | |
|-------------|----------|-----------------------|---|--|----|----|----|-----|-----|-----|----|--------|----|----|-----|-----|-----|----|----|--------|----|-----|-----|-----|----|----|----|----|----|----|----|
| | | Voltage Code | | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | 8 | 4 | 3 | 5 | 1 | 2 | A | | | | | | | |
| | | Rated Voltage (VDC) | | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 | | | | | | | |
| | | Capacitance Tolerance | | Product Availability and Chip Thickness Codes See Table 2 for Chip Thickness Dimensions | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 180 pF | 181 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 200 pF | 201 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 220 pF | 221 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 240 pF | 241 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 270 pF | 271 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 300 pF | 301 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 330 pF | 331 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 360 pF | 361 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 390 pF | 391 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 430 pF | 431 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 470 pF | 471 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DD | DD | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 510 pF | 511 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 560 pF | 561 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 620 pF | 621 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 680 pF | 681 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 750 pF | 751 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 820 pF | 821 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 910 pF | 911 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DR | DD | DD | DD | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 1,000 pF | 102 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | CJ | DR | DR | DR | DR | DD | DD | DD | DD | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 1,100 pF | 112 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 1,200 pF | 122 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 1,300 pF | 132 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DD | DD | DD | DD | DR | DR | EQ | EQ | EQ | EQ | EQ | ER | ER | ER | ER |
| 1,500 pF | 152 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DD | DD | DD | DD | DR | DR | EQ | EQ | EQ | EQ | EQ | ES | ER | ER | ER |
| 1,600 pF | 162 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DD | DD | DD | DD | DR | DR | EQ | EQ | EQ | EQ | EQ | ES | ES | ES | ES |
| 1,800 pF | 182 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DD | DD | DD | DR | DR | DR | DR | EQ | EQ | EQ | EQ | ES | ES | ES | ES |
| 2,000 pF | 202 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | ES | ES | ES | ES |
| 2,200 pF | 222 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | ET | ET | ET | ET |
| 2,400 pF | 242 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | ER | ER | ER | ER |
| 2,700 pF | 272 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DR | DR | DR | EQ | EQ | EQ | EQ | EQ | ER | ER | ER | ER |
| 3,000 pF | 302 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DR | DR | DR | DR | DR | DR | ER | ER | ER | ER | ER | ER | EQ | EQ | EQ |
| 3,300 pF | 332 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DR | DR | DR | DR | DR | DR | ER | ER | ER | ER | ER | ET | EQ | EQ | EQ |
| 3,600 pF | 362 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DR | DR | DR | DR | DD | DD | ER | ER | ER | ER | ER | ET | EQ | EQ | EQ |
| 3,900 pF | 392 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DS | DS | DR | DR | DR | DR | DD | DD | ER | ER | ER | ER | ER | EF | EQ | EQ | EQ |
| 4,300 pF | 432 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DS | DS | DR | DR | DR | DD | DD | DD | ER | ER | ER | ER | ER | ER | EQ | EQ | EQ |
| 4,700 pF | 472 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DS | DS | DR | DR | DR | DD | DD | DD | ER | ER | ER | ER | ER | ER | EQ | EQ | EQ |
| 5,100 pF | 512 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DS | DS | DR | DR | DR | DD | DD | DD | ES | ES | ES | ES | ES | ES | EQ | EQ | EQ |
| 5,600 pF | 562 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DD | DD | DD | ES | ES | ES | ES | ES | ES | EQ | EQ | EQ |
| 6,200 pF | 622 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 6,800 pF | 682 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 7,500 pF | 752 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ | EQ |
| 8,200 pF | 822 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DG | DG | DG | ER | ER | ER | ER | ER | EQ | ER | ER | ER |
| 9,100 pF | 912 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DR | DG | DG | DG | ER | ER | EQ | EQ | EQ | EQ | ER | ER | ER |
| 10,000 pF | 103 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DD | DD | DD | DD | EQ | EQ | EQ | EQ | EQ | EQ | ER | ER | ER |
| 12,000 pF | 123 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DR | DS | DS | DS | DS | EQ | EQ | EQ | EQ | EQ | EQ | ES | ES | ES |
| 15,000 pF | 153 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DD | DG | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | EF | EF | EF |
| 18,000 pF | 183 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DR | DR | DR | DD | DG | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | EH | EH | EH |
| 22,000 pF | 223 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DD | DD | DD | DF | DF | DF | DF | DF | EQ | EQ | EQ | EQ | EQ | ER | EH | EH | EH |
| 27,000 pF | 273 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DF | DF | DF | DF | DF | DF | DF | DF | EQ | EQ | EQ | EQ | EQ | ET | ET | ET | ET |
| 33,000 pF | 333 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DG | DG | DG | DG | DG | DG | DG | DG | EQ | EQ | EQ | EQ | EQ | EQ | ET | ET | ET |
| 39,000 pF | 393 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DG | DG | DG | DG | DG | DG | DG | DG | ER | ER | ER | ET | EH | EH | EH | EH | EH |
| 47,000 pF | 473 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | DG | DG | DG | DG | DG | DG | DG | DG | ER | ER | ER | ET | EH | EH | EH | EH | EH |
| 56,000 pF | 563 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | ES | ES | ES | ES | ES | ES | ES | ES | ES | ES | ES | ES | EF | EF | EF | EF | EF |
| 68,000 pF | 683 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH |
| 82,000 pF | 823 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH |
| 100,000 pF | 104 | F | G | J | K | M | CJ | CJ | CJ | CJ | CJ | CH | CH | CH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH | EH |

Performance and Reliability: Test Methods and Conditions

| Test | Reference | Test Condition | Limits | | | | | | | | | | |
|---|-------------------|--|--|------------------|---|-------|---|-------|---|-------------------|---|--------|--|
| Visual and Mechanical | KEMET Internal | No defects that may affect performance (10X) | Dimensions according KEMET Spec Sheet | | | | | | | | | | |
| Capacitance (Cap) | KEMET Internal | $C \leq 1,000 \text{ pF}$ Frequency: 1 MHz $\pm 100 \text{ kHz}$ Voltage*: $1.0 V_{\text{rms}} \pm 0.2 \text{ V}$ $C > 1,000 \text{ pF}$ Frequency: 1 kHz $\pm 50 \text{ Hz}$ Voltage: $1.0 V_{\text{rms}} \pm 0.2 \text{ V}$ * See part number specification sheet for voltage | Within Tolerance | | | | | | | | | | |
| Dissipation Factor (DF) | KEMET Internal | $C \leq 1,000 \text{ pF}$ Frequency: 1 MHz $\pm 100 \text{ kHz}$ Voltage*: $1.0 V_{\text{rms}} \pm 0.2 \text{ V}$ $C > 1,000 \text{ pF}$ Frequency: 1 kHz $\pm 50 \text{ Hz}$ Voltage: $1.0 V_{\text{rms}} \pm 0.2 \text{ V}$ * See part number specification sheet for voltage" | Within Specification Dissipation factor (DF) maximum limit at 25°C = 0.1% | | | | | | | | | | |
| Insulation Resistance (IR) | KEMET Internal | Rated voltage applied for 120 ± 5 seconds at 25°C | Within Specification To obtain IR limit, divide M Ω - μF value by the capacitance and compare to G Ω limit. Select the lower of the two limits. 1,000 megaohm microfarads or 100 G Ω . | | | | | | | | | | |
| Temperature Coefficient of Capacitance (TCC) | KEMET Internal | Capacitance change with reference to +25°C and 0 VDC applied. * See part number specification sheet for voltage <table border="1" style="margin: 10px auto;"> <thead> <tr> <th>Step</th> <th>Temperature (°C)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>+25°C</td> </tr> <tr> <td>2</td> <td>-55°C</td> </tr> <tr> <td>3</td> <td>+25°C (Reference)</td> </tr> <tr> <td>4</td> <td>+150°C</td> </tr> </tbody> </table> | Step | Temperature (°C) | 1 | +25°C | 2 | -55°C | 3 | +25°C (Reference) | 4 | +150°C | Within Specification $\pm 30 \text{ ppm}/^\circ\text{C}$ *Except :1210 Cap Code ≥ 682 ; 1812 Cap Code ≥ 471 ; 2220 Cap Code ≥ 682 $\pm 30 \text{ ppm}/^\circ\text{C}$ from -55°C to +125°C; $\pm 60 \text{ ppm}/^\circ\text{C}$ from +125°C to +150°C |
| Step | Temperature (°C) | | | | | | | | | | | | |
| 1 | +25°C | | | | | | | | | | | | |
| 2 | -55°C | | | | | | | | | | | | |
| 3 | +25°C (Reference) | | | | | | | | | | | | |
| 4 | +150°C | | | | | | | | | | | | |
| Dielectric Withstanding Voltage (DWV) | KEMET Internal | 250% of rated voltage (5 ± 1 seconds and charge/discharge not exceeding 50 mA) | Cap: Initial Limit DF: Initial Limit IR: Initial Limit Withstand test voltage without insulation breakdown or damage. | | | | | | | | | | |
| Aging Rate (Maximum % Capacitance Loss/Decade Hour) | KEMET Internal | Maximum % capacitance loss/decade hour | 0% Loss/Decade Hour | | | | | | | | | | |

Performance and Reliability: Test Methods and Conditions cont.

| Test | Reference | Test Condition | Limits | | | | | | | | | | |
|-----------------------|------------------------|---|--|-------|------|----|------|----|------|----|-------|-----|----------------------------------|
| Terminal Strength | KEMET Internal | Shear stress test per specific case size, Time: 60±1 seconds <table border="1"> <thead> <tr> <th>Case Size</th> <th>Force</th> </tr> </thead> <tbody> <tr> <td>0402</td> <td>3N</td> </tr> <tr> <td>0603</td> <td>5N</td> </tr> <tr> <td>0805</td> <td>9N</td> </tr> <tr> <td>≥1206</td> <td>18N</td> </tr> </tbody> </table>  | Case Size | Force | 0402 | 3N | 0603 | 5N | 0805 | 9N | ≥1206 | 18N | No evidence of mechanical damage |
| Case Size | Force | | | | | | | | | | | | |
| 0402 | 3N | | | | | | | | | | | | |
| 0603 | 5N | | | | | | | | | | | | |
| 0805 | 9N | | | | | | | | | | | | |
| ≥1206 | 18N | | | | | | | | | | | | |
| Board Flex | AEC-Q200-005 | 3.0 mm minimum Test time: 60± 5 seconds Ramp time: 1 mm/second  | No evidence of mechanical damage | | | | | | | | | | |
| Solderability | J-STD-002 | Condition: 4 hours ± 15 minimum at 155°C dry bake apply all methods Test 245 ± 5°C (SnPb & Pb-Free) | Visual Inspection. 95% coverage on termination. No leaching | | | | | | | | | | |
| Temperature Cycling | JESD22 Method JA-104 | 1,000 cycles (-55°C to +150°C) 2 – 3 cycles per hour Soak Time 1 or 5 minutes | Measurement at 24 hours ±4 hours after test conclusion. Cap: Initial Limit DF: Initial Limit IR: Initial Limit | | | | | | | | | | |
| Biased Humidity | MIL-STD-202 Method 103 | Load Humidity: 1,000 hours 85°C/85% RH and 200 VDC maximum. Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. | Measurement at 24 hours ±4 hours after test conclusion. Within Post Environmental Limits Cap: ±0.3% or ±0.25 pF shift IR: 10% of Initial Limit DF Limits Maximum: 0.5% | | | | | | | | | | |
| Moisture Resistance | MIL-STD-202 Method 106 | Number of cycles required 10, 24 hours per cycle. Steps 7a and 7b not required | Measurement at 24 hours ±4 hours after test conclusion. Within Post Environmental Limits Cap: ±0.3% or ±0.25 pF shift IR: 10% of Initial Limit DF Limits Maximum: 0.5% | | | | | | | | | | |
| Thermal Shock | MIL-STD-202 Method 107 | Number of cycles required 5, (-55°C to 150°C) Dwell time 15 minutes. | Cap: Initial Limit DF: Initial Limit IR: Initial Limit | | | | | | | | | | |
| High Temperature Life | MIL-STD-202 Method 108 | 1,000 hours at 150°C with 2 X rated voltage applied | Within Post Environmental Limits Cap: ±0.3% or ±0.25 pF shift IR: 10% of Initial Limit DF: 0.5% | | | | | | | | | | |
| Storage Life | | 1,000 hours at 150°C, Unpowered | | | | | | | | | | | |

Performance and Reliability: Test Methods and Conditions cont.

| Test | Reference | Test Condition | Limits |
|------------------------|------------------------|---|---|
| Vibration | MIL-STD-202 Method 204 | 5 g's for 20 minutes, 12 cycles each of 3 orientations. Test from 10 – 2,000 Hz | Cap: Initial Limit DF: Initial Limit IR: Initial Limit |
| Mechanical Shock | MIL-STD-202 Method 213 | 1,500 g's 0.5 ms Half-sine, Velocity Change 15.4 feet/second (Condition F) | Cap: Initial Limit DF: Initial Limit IR: Initial Limit |
| Resistance to Solvents | MIL-STD-202 Method 215 | Add Aqueous wash chemical OKEMCLEAN (A 6% concentrated Oakite cleaner) or equivalent. Do not use banned solvents. | Visual Inspection 10X Readable marking, no decoloration or stains. No physical damage. |

Table 2A – Standard Termination Chip Thickness/Tape & Reel Packaging Quantities

| Thickness Code | Case Size ¹ | Thickness ± Range (mm) | Paper Quantity ¹ | | Plastic Quantity | |
|----------------|------------------------|------------------------|-----------------------------|----------|------------------|----------|
| | | | 7" Reel | 13" Reel | 7" Reel | 13" Reel |
| BB | 0402 | 0.50 ± 0.05 | 10,000 | 50,000 | 0 | 0 |
| BD | 0402 | 0.55 ± 0.05 | 10,000 | 50,000 | 0 | 0 |
| CF | 0603 | 0.80 ± 0.07 | 4,000 | 15,000 | 0 | 0 |
| CH | 0603 | 0.85 ± 0.07 | 4,000 | 10,000 | 0 | 0 |
| DN | 0805 | 0.78 ± 0.10 | 4,000 | 15,000 | 0 | 0 |
| DP | 0805 | 0.90 ± 0.10 | 4,000 | 15,000 | 0 | 0 |
| DE | 0805 | 1.00 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| DF | 0805 | 1.10 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| DG | 0805 | 1.25 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| EB | 1206 | 0.78 ± 0.10 | 0 | 0 | 4,000 | 10,000 |
| EC | 1206 | 0.90 ± 0.10 | 0 | 0 | 4,000 | 10,000 |
| ED | 1206 | 1.00 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| EE | 1206 | 1.10 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| EF | 1206 | 1.20 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| EH | 1206 | 1.60 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| FB | 1210 | 0.78 ± 0.10 | 0 | 0 | 4,000 | 10,000 |
| FC | 1210 | 0.90 ± 0.10 | 0 | 0 | 4,000 | 10,000 |
| FE | 1210 | 1.00 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| FF | 1210 | 1.10 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| FG | 1210 | 1.25 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| FH | 1210 | 1.55 ± 0.15 | 0 | 0 | 2,000 | 8,000 |
| FM | 1210 | 1.70 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| FJ | 1210 | 1.85 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| GB | 1812 | 1.00 ± 0.10 | 0 | 0 | 1,000 | 4,000 |
| GD | 1812 | 1.25 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GH | 1812 | 1.40 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GG | 1812 | 1.55 ± 0.10 | 0 | 0 | 1,000 | 4,000 |
| GK | 1812 | 1.60 ± 0.20 | 0 | 0 | 1,000 | 4,000 |
| GJ | 1812 | 1.70 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GN | 1812 | 1.70 ± 0.20 | 0 | 0 | 1,000 | 4,000 |
| GM | 1812 | 2.00 ± 0.20 | 0 | 0 | 500 | 2,000 |
| JB | 2220 | 1.00 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JD | 2220 | 1.30 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JE | 2220 | 1.40 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JF | 2220 | 1.50 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JG | 2220 | 1.70 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JL | 2220 | 2.00 ± 0.20 | 0 | 0 | 500 | 2,000 |
| Thickness Code | Case Size ¹ | Thickness ± Range (mm) | 7" Reel | 13" Reel | 7" Reel | 13" Reel |
| | | | Paper Quantity ¹ | | Plastic Quantity | |

Package quantity based on finished chip thickness specifications.

¹ If ordering using the 2 mm Tape and Reel pitch option, the packaging quantity outlined in the table above will be doubled. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".

Table 2B – Flexible Termination Chip Thickness/Tape & Reel Packaging Quantities

| Thickness Code | Case Size ¹ | Thickness ± Range (mm) | Paper Quantity ¹ | | Plastic Quantity | |
|----------------|------------------------|------------------------|-----------------------------|----------|------------------|----------|
| | | | 7" Reel | 13" Reel | 7" Reel | 13" Reel |
| CJ | 0603 | 0.80 ± 0.15 | 4,000 | 15,000 | 0 | 0 |
| CH | 0603 | 0.85 ± 0.07 | 4,000 | 10,000 | 0 | 0 |
| DR | 0805 | 0.78 ± 0.20 | 0 | 0 | 4,000 | 10,000 |
| DD | 0805 | 0.90 ± 0.10 | 0 | 0 | 4,000 | 10,000 |
| DS | 0805 | 1.00 ± 0.20 | 0 | 0 | 2,500 | 10,000 |
| DF | 0805 | 1.10 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| DG | 0805 | 1.25 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| EQ | 1206 | 0.78 ± 0.20 | 0 | 0 | 4,000 | 10,000 |
| ER | 1206 | 0.90 ± 0.20 | 0 | 0 | 4,000 | 10,000 |
| ES | 1206 | 1.00 ± 0.20 | 0 | 0 | 2,500 | 10,000 |
| ET | 1206 | 1.10 ± 0.20 | 0 | 0 | 2,500 | 10,000 |
| EF | 1206 | 1.20 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| EH | 1206 | 1.60 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| FN | 1210 | 0.78 ± 0.20 | 0 | 0 | 4,000 | 10,000 |
| FQ | 1210 | 0.90 ± 0.20 | 0 | 0 | 4,000 | 10,000 |
| FE | 1210 | 1.00 ± 0.10 | 0 | 0 | 2,500 | 10,000 |
| FA | 1210 | 1.10 ± 0.15 | 0 | 0 | 2,500 | 10,000 |
| FZ | 1210 | 1.25 ± 0.20 | 0 | 0 | 2,500 | 10,000 |
| FU | 1210 | 1.55 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| FM | 1210 | 1.70 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| FJ | 1210 | 1.85 ± 0.20 | 0 | 0 | 2,000 | 8,000 |
| GB | 1812 | 1.00 ± 0.10 | 0 | 0 | 1,000 | 4,000 |
| GD | 1812 | 1.25 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GH | 1812 | 1.40 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GG | 1812 | 1.55 ± 0.10 | 0 | 0 | 1,000 | 4,000 |
| GK | 1812 | 1.60 ± 0.20 | 0 | 0 | 1,000 | 4,000 |
| GJ | 1812 | 1.70 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| GN | 1812 | 1.70 ± 0.20 | 0 | 0 | 1,000 | 4,000 |
| GM | 1812 | 2.00 ± 0.20 | 0 | 0 | 500 | 2,000 |
| JB | 2220 | 1.00 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JD | 2220 | 1.30 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JE | 2220 | 1.40 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JF | 2220 | 1.50 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JG | 2220 | 1.70 ± 0.15 | 0 | 0 | 1,000 | 4,000 |
| JL | 2220 | 2.00 ± 0.20 | 0 | 0 | 500 | 2,000 |
| Thickness Code | Case Size ¹ | Thickness ± Range (mm) | 7" Reel | 13" Reel | 7" Reel | 13" Reel |
| | | | Paper Quantity ¹ | | Plastic Quantity | |

Package quantity based on finished chip thickness specifications.

¹ If ordering using the 2 mm Tape and Reel pitch option, the packaging quantity outlined in the table above will be doubled. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".

Table 2C – Bulk Packaging Quantities

| Packaging Type | | Loose Packaging | |
|-------------------------------|-------------|--|---------|
| | | Bulk Bag (default) | |
| Packaging C-Spec ¹ | | N/A ² | |
| Case Size | | Packaging Quantities (pieces/unit packaging) | |
| EIA (in) | Metric (mm) | Minimum | Maximum |
| 0402 | 1005 | 1 | 50,000 |
| 0603 | 1608 | | |
| 0805 | 2012 | | |
| 1206 | 3216 | | |
| 1210 | 3225 | | |
| 1808 | 4520 | | 20,000 |
| 1812 | 4532 | | |
| 1825 | 4564 | | |
| 2220 | 5650 | | |
| 2225 | 5664 | | |

¹ The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

² A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.

Table 3 – Standard Termination Chip Capacitor Land Pattern Design Recommendations per IPC-7351

| EIA Size Code | Metric Size Code | Density Level A: Maximum (Most) Land Protrusion (mm) | | | | | Density Level B: Median (Nominal) Land Protrusion (mm) | | | | | Density Level C: Minimum (Least) Land Protrusion (mm) | | | | |
|-------------------|------------------|--|------|------|------|------|--|------|------|------|------|---|------|------|------|------|
| | | C | Y | X | V1 | V2 | C | Y | X | V1 | V2 | C | Y | X | V1 | V2 |
| 0402 | 1005 | 0.50 | 0.72 | 0.72 | 2.20 | 1.20 | 0.45 | 0.62 | 0.62 | 1.90 | 1.00 | 0.40 | 0.52 | 0.52 | 1.60 | 0.80 |
| 0603 | 1608 | 0.90 | 1.15 | 1.10 | 4.00 | 2.10 | 0.80 | 0.95 | 1.00 | 3.10 | 1.50 | 0.60 | 0.75 | 0.90 | 2.40 | 1.20 |
| 0805 | 2012 | 1.00 | 1.35 | 1.55 | 4.40 | 2.60 | 0.90 | 1.15 | 1.45 | 3.50 | 2.00 | 0.75 | 0.95 | 1.35 | 2.80 | 1.70 |
| 1206 | 3216 | 1.60 | 1.35 | 1.90 | 5.60 | 2.90 | 1.50 | 1.15 | 1.80 | 4.70 | 2.30 | 1.40 | 0.95 | 1.70 | 4.00 | 2.00 |
| 1210 | 3225 | 1.60 | 1.35 | 2.80 | 5.65 | 3.80 | 1.50 | 1.15 | 2.70 | 4.70 | 3.20 | 1.40 | 0.95 | 2.60 | 4.00 | 2.90 |
| 1210 ¹ | 3225 | 1.50 | 1.60 | 2.90 | 5.60 | 3.90 | 1.40 | 1.40 | 2.80 | 4.70 | 3.30 | 1.30 | 1.20 | 2.70 | 4.00 | 3.00 |
| 1812 | 4532 | 2.15 | 1.60 | 3.60 | 6.90 | 4.60 | 2.05 | 1.40 | 3.50 | 6.00 | 4.00 | 1.95 | 1.20 | 3.40 | 5.30 | 3.70 |
| 2220 | 5650 | 2.75 | 1.70 | 5.50 | 8.20 | 6.50 | 2.65 | 1.50 | 5.40 | 7.30 | 5.90 | 2.55 | 1.30 | 5.30 | 6.60 | 5.60 |

¹ Only for capacitance values $\geq 22 \mu\text{F}$.

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

Density Level C: For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.




Table 4 – Flexible Termination Chip Capacitor Land Pattern Design Recommendations per IPC-7351 (mm)


| EIA Size Code | Metric Size Code | Density Level A: Maximum (Most) Land Protrusion (mm) | | | | | Density Level B: Median (Nominal) Land Protrusion (mm) | | | | | Density Level C: Minimum (Least) Land Protrusion (mm) | | | | |
|---------------|------------------|--|------|------|------|------|--|------|------|------|------|---|------|------|------|------|
| | | C | Y | X | V1 | V2 | C | Y | X | V1 | V2 | C | Y | X | V1 | V2 |
| 0603 | 1608 | 0.85 | 1.25 | 1.10 | 4.00 | 2.10 | 0.75 | 1.05 | 1.00 | 3.10 | 1.50 | 0.65 | 0.85 | 0.90 | 2.40 | 1.20 |
| 0805 | 2012 | 0.99 | 1.44 | 1.66 | 4.47 | 2.71 | 0.89 | 1.24 | 1.56 | 3.57 | 2.11 | 0.79 | 1.04 | 1.46 | 2.42 | 1.81 |
| 1206 | 3216 | 1.59 | 1.62 | 2.06 | 5.85 | 3.06 | 1.49 | 1.42 | 1.96 | 4.95 | 2.46 | 1.39 | 1.22 | 1.86 | 4.25 | 2.16 |
| 1210 | 3225 | 1.59 | 1.62 | 3.01 | 5.90 | 4.01 | 1.49 | 1.42 | 2.91 | 4.95 | 3.41 | 1.39 | 1.22 | 2.81 | 4.25 | 3.11 |
| 1808 | 4520 | 2.30 | 1.75 | 2.30 | 7.40 | 3.30 | 2.20 | 1.55 | 2.20 | 6.50 | 2.70 | 2.10 | 1.35 | 2.10 | 5.80 | 2.40 |
| 1812 | 4532 | 2.10 | 1.80 | 3.60 | 7.00 | 4.60 | 2.00 | 1.60 | 3.50 | 6.10 | 4.00 | 1.90 | 1.40 | 3.40 | 5.40 | 3.70 |
| 2220 | 5650 | 2.85 | 2.10 | 5.50 | 8.80 | 6.50 | 2.75 | 1.90 | 5.40 | 7.90 | 5.90 | 2.65 | 1.70 | 5.30 | 7.20 | 5.60 |

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805, and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

Density Level C: For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.



Soldering Process

Recommended Soldering Technique:


- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- All other EIA case sizes are limited to solder reflow only

Recommended Reflow Soldering Profile:

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

| Profile Feature | Termination Finish | |
|---|--------------------|--------------------|
| | SnPb | 100% Matte Sn |
| Preheat/Soak | | |
| Temperature Minimum (T_{Smin}) | 100°C | 150°C |
| Temperature Maximum (T_{Smax}) | 150°C | 200°C |
| Time (t_s) from T_{Smin} to T_{Smax} | 60 – 120 seconds | 60 – 120 seconds |
| Ramp-Up Rate (T_L to T_p) | 3°C/second maximum | 3°C/second maximum |
| Liquidous Temperature (T_L) | 183°C | 217°C |
| Time Above Liquidous (t_L) | 60 – 150 seconds | 60 – 150 seconds |
| Peak Temperature (T_p) | 235°C | 260°C |
| Time Within 5°C of Maximum Peak Temperature (t_p) | 20 seconds maximum | 30 seconds maximum |
| Ramp-Down Rate (T_p to T_L) | 6°C/second maximum | 6°C/second maximum |
| Time 25°C to Peak Temperature | 6 minutes maximum | 8 minutes maximum |

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.




Storage and Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature – reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.


Construction

Standard Termination



Construction cont.

Flex Termination



Capacitor Marking (Optional)

Laser marking option is not available on:

- COG, U2J, X8G, X8R and Y5V dielectric devices.
- EIA 0402 case size devices.
- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.

Tape & Reel Packaging Information

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.




Table 5 – Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

| EIA Case Size | Tape Size (W)* | Embossed Plastic | | Punched Paper | |
|-------------------|----------------|--------------------------|----------|--------------------------|----------|
| | | 7" Reel | 13" Reel | 7" Reel | 13" Reel |
| | | Pitch (P ₁)* | | Pitch (P ₁)* | |
| 01005 – 0402 | 8 | | | 2 | 2 |
| 0603 | 8 | | | 2/4 | 2/4 |
| 0805 | 8 | 4 | 4 | 4 | 4 |
| 1206 – 1210 | 8 | 4 | 4 | 4 | 4 |
| 1805 – 1808 | 12 | 4 | 4 | | |
| ≥ 1812 | 12 | 8 | 8 | | |
| KPS 1210 | 12 | 8 | 8 | | |
| KPS 1812 and 2220 | 16 | 12 | 12 | | |
| Array 0612 | 8 | 4 | 4 | | |

New 2 mm Pitch Reel Options*

| Packaging Ordering Code (C-Spec) | Packaging Type/Options |
|----------------------------------|------------------------------------|
| C-3190 | Automotive grade 7" reel unmarked |
| C-3191 | Automotive grade 13" reel unmarked |
| C-7081 | Commercial grade 7" reel unmarked |
| C-7082 | Commercial grade 13" reel unmarked |

* 2 mm pitch reel only available for 0603 EIA case size.
 2 mm pitch reel for 0805 EIA case size under development.

Benefits of Changing from 4 mm to 2 mm Pitching Spacing

- Lower placement costs.
- Double the parts on each reel results in fewer reel changes and increased efficiency.
- Fewer reels result in lower packaging, shipping and storage costs, reducing waste.

*Refer to Figures 1 and 2 for W and P₁ carrier tape reference locations.
 *Refer to Tables 6 and 7 for tolerance specifications.

Figure 1 – Embossed (Plastic) Carrier Tape Dimensions




Table 6 – Embossed (Plastic) Carrier Tape Dimensions
 Metric will govern

| Constant Dimensions – Millimeters (Inches) | | | | | | | | | |
|--|---------------------------------------|----------------------------------|------------------------------|-----------------------------|------------------------------|---------------------------|----------------------------------|--|---------------------------|
| Tape Size | D ₀ | D ₁ Minimum Note 1 | E ₁ | P ₀ | P ₂ | R Reference Note 2 | S ₁ Minimum Note 3 | T Maximum | T ₁ Maximum |
| 8 mm | 1.5 +0.10/-0.0 (0.059 +0.004/-0.0) | 1.0 (0.039) | 1.75 ±0.10 (0.069 ±0.004) | 4.0 ±0.10 (0.157 ±0.004) | 2.0 ±0.05 (0.079 ±0.002) | 25.0 (0.984) | 0.600 (0.024) | 0.600 (0.024) | 0.100 (0.004) |
| 12 mm | | 1.5 (0.059) | | | | | | | |
| 16 mm | | | | | | | | | |
| Variable Dimensions – Millimeters (Inches) | | | | | | | | | |
| Tape Size | Pitch | B ₁ Maximum Note 4 | E ₂ Minimum | F | P ₁ | T ₂ Maximum | W Maximum | A ₀ , B ₀ & K ₀ | |
| 8 mm | Single (4 mm) | 4.35 (0.171) | 6.25 (0.246) | 3.5 ±0.05 (0.138 ±0.002) | 4.0 ±0.10 (0.157 ±0.004) | 2.5 (0.098) | 8.3 (0.327) | Note 5 | |
| 12 mm | Single (4 mm) and double (8 mm) | 8.2 (0.323) | 10.25 (0.404) | 5.5 ±0.05 (0.217 ±0.002) | 8.0 ±0.10 (0.315 ±0.004) | 4.6 (0.181) | 12.3 (0.484) | | |
| 16 mm | Triple (12 mm) | 12.1 (0.476) | 14.25 (0.561) | 7.5 ±0.05 (0.138 ±0.002) | 12.0 ±0.10 (0.157 ±0.004) | 4.6 (0.181) | 16.3 (0.642) | | |

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of the embossment location and the hole location shall be applied independently of each other.
2. The tape with or without components shall pass around R without damage (see Figure 6.)
3. If S₁ < 1.0 mm, there may not be enough area for a cover tape to be properly applied (see EIA Standard 481, paragraph 4.3, section b.)
4. B₁ dimension is a reference dimension for tape feeder clearance only.
5. The cavity defined by A₀, B₀ and K₀ shall surround the component with sufficient clearance that:
 - (a) the component does not protrude above the top surface of the carrier tape.
 - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3.)
 - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4.)
 - (e) for KPS product, A₀ and B₀ are measured on a plane 0.3 mm above the bottom of the pocket.
 - (f) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.

Figure 2 – Punched (Paper) Carrier Tape Dimensions




Table 7 – Punched (Paper) Carrier Tape Dimensions

Metric will govern

| Constant Dimensions – Millimeters (Inches) | | | | | | | |
|--|---------------------------------------|------------------------------|-----------------------------|-----------------------------|----------------------------|-----------------|--------------------|
| Tape Size | D_0 | E_1 | P_0 | P_2 | T_1 Maximum | G Minimum | R Reference Note 2 |
| 8 mm | 1.5 +0.10 -0.0 (0.059 +0.004 -0.0) | 1.75 ±0.10 (0.069 ±0.004) | 4.0 ±0.10 (0.157 ±0.004) | 2.0 ±0.05 (0.079 ±0.002) | 0.10 (0.004) maximum | 0.75 (0.030) | 25 (0.984) |
| Variable Dimensions – Millimeters (Inches) | | | | | | | |
| Tape Size | Pitch | E2 Minimum | F | P_1 | T Maximum | W Maximum | $A_0 B_0$ |
| 8 mm | Half (2 mm) | 6.25 (0.246) | 3.5 ±0.05 (0.138 ±0.002) | 2.0 ±0.05 (0.079 ±0.002) | 1.1 (0.098) | 8.3 (0.327) | Note 1 |
| 8 mm | Single (4 mm) | | | 4.0 ±0.10 (0.157 ±0.004) | | | |

- The cavity defined by A_0 , B_0 and T shall surround the component with sufficient clearance that:
 - the component does not protrude beyond either surface of the carrier tape.
 - the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - rotation of the component is limited to 20° maximum (see Figure 3.)
 - lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4.)
 - see addendum in EIA Standard 481 for standards relating to more precise taping requirements.
- The tape with or without components shall pass around R without damage (see Figure 6.)

Packaging Information Performance Notes

- Cover Tape Break Force:** 1.0 kg minimum.
- Cover Tape Peel Strength:** The total peel strength of the cover tape from the carrier tape shall be:

| Tape Width | Peel Strength |
|--------------|----------------------------------|
| 8 mm | 0.1 to 1.0 newton (10 to 100 gf) |
| 12 and 16 mm | 0.1 to 1.3 newton (10 to 130 gf) |

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

- Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. Refer to EIA Standards 556 and 624.

Figure 3 – Maximum Component Rotation




Figure 4 – Maximum Lateral Movement




Figure 5 – Bending Radius





Figure 6 – Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.

Table 8 – Reel Dimensions

Metric will govern

| Constant Dimensions – Millimeters (Inches) | | | | |
|--|---|---------------------------------------|--|---|
| Tape Size | A | B Minimum | C | D Minimum |
| 8 mm | 178 ±0.20 (7.008 ±0.008) or 330 ±0.20 (13.000 ±0.008) | 1.5 (0.059) | 13.0 +0.5/-0.2 (0.521 +0.02/-0.008) | 20.2 (0.795) |
| 12 mm | | | | |
| 16 mm | | | | |
| Variable Dimensions – Millimeters (Inches) | | | | |
| Tape Size | N Minimum | W ₁ | W ₂ Maximum | W ₃ |
| 8 mm | 50 (1.969) | 8.4 +1.5/-0.0 (0.331 +0.059/-0.0) | 14.4 (0.567) | Shall accommodate tape width without interference |
| 12 mm | | 12.4 +2.0/-0.0 (0.488 +0.078/-0.0) | 18.4 (0.724) | |
| 16 mm | | 16.4 +2.0/-0.0 (0.646 +0.078/-0.0) | 22.4 (0.882) | |

Figure 7 – Tape Leader & Trailer Dimensions





Figure 8 – Maximum Camber



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.