# **COG Dielectric, 10 – 250 VDC (Commercial Grade)**




#### **Overview**

KEMET's COG dielectric features a 125°C maximum operating temperature and is considered "stable." The Electronics Components, Assemblies & Materials Association (EIA) characterizes COG dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant

circuit applications or those where Q and stability of capacitance characteristics are required. COG exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to ±30 ppm/°C from -55°C to +125°C.

#### **Benefits**

- -55°C to +125°C operating temperature range
- · Lead (Pb)-free, RoHS, and REACH compliant
- EIA 0201, 0402, 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, and 2225 case sizes
- DC voltage ratings of 10 V, 16 V, 25 V, 50 V, 100 V, 200 V, and 250 V
- Capacitance offerings ranging from 0.5 pF up to 0.47  $\mu F$
- Available capacitance tolerances of ±0.10 pF, ±0.25 pF, ±0.5 pF, ±1%, ±2%, ±5%, ±10%, and ±20%
- · No piezoelectric noise
- Extremely low ESR and ESL
- · High thermal stability
- High ripple current capability



# **Ordering Information**

C	1206	С	104	J	3	G	Α	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series <sup>1</sup>	Capacitance Code (pF)	Capacitance Tolerance <sup>2</sup>	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish <sup>3</sup>	Packaging/ Grade (C-Spec)
	0201 0402 0603 0805 1206 1210 1805 1808 1812 1825 2220 2225	C = Standard	Two significant digits and number of zeros. Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – .99 pF e.g., 2.2 pF = 229 e.g., 0.5 pF = 508	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = COG	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table"

<sup>&</sup>lt;sup>1</sup> Flexible termination option is available. Please see FT-CAP product bulletin C1062\_C0G\_FT-CAP\_SMD

<sup>&</sup>lt;sup>2</sup> Additional capacitance tolerance offerings may be available. Contact KEMET for details.

<sup>&</sup>lt;sup>3</sup> Additional termination finish options may be available. Contact KEMET for details.



# **Packaging C-Spec Ordering Options Table**

Packaging Type <sup>1</sup>	Packaging/Grade Ordering Code (C-Spec)
Bulk Bag/Unmarked	Not required (Blank)
7" Reel/Unmarked	TU
13" Reel/Unmarked	7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes)

<sup>&</sup>lt;sup>1</sup> Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

#### Benefits cont.

- Preferred capacitance solution at line frequencies and into the MHz range
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- · No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb plated termination finish option available upon request (5% Pb minimum)

# **Applications**

Typical applications include critical timing, tuning, circuits requiring low loss, circuits with pulse, high current, decoupling, bypass, filtering, transient voltage suppression, blocking and energy storage.

#### **Qualification/Certification**

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance and Reliability.


# **Environmental Compliance**

Lead (Pb)-free, RoHS, and REACH compliant without exemptions.

<sup>&</sup>lt;sup>1</sup> The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked. The option to laser mark is not available on these devices. For more information see "Capacitor Marking".



# **Dimensions - Millimeters (Inches)**



EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique
0201	0603	0.60 (0.024) ±0.03 (0.001)	0.30 (0.012) ±0.03 (0.001)		0.15 (0.006) ±0.05 (0.002)	N/A	Solder Reflow
0402	1005	1.00 (0.040) ±0.05 (0.002)	0.50 (0.020) ±0.05 (0.002)		0.30 (0.012) ±0.10 (0.004)	0.30 (0.012)	Only
0603	1608	1.60 (0.063) ±0.15 (0.006)	0.80 (0.032) ±0.15 (0.006)		0.35 (0.014) ±0.15 (0.006)	0.50 (0.020)	
0805	2012	2.00 (0.079) ±0.20 (0.008)	1.25 (0.049) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	0.70 (0.028)	Solder Wave or Solder Reflow
11206	3216	3.20 (0.126) ±0.20 (0.008)	1.60 (0.063) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	1.50 (0.060)	
1210	3225	3.20 (0.126) ±0.20 (0.008)	2.50 (0.098) ±0.20 (0.008)	See Table 2 for	0.50 (0.02) ±0.25 (0.010)	1.50 (0.060)	
1805	4513	4.50 (0.177) ±0.50 (0.020)	1.27 (0.050) ±0.38 (0.015)	Thickness	0.60 (0.024) ±0.35 (0.014)	2.90 (0.114)	
1808	4520	4.70 (0.185) ±0.50 (0.020)	2.00 (0.079) ±0.20 (0.008)		0.60 (0.024) ±0.35 (0.014)	2.90 (0.114)	
1812	4532	4.50 (0.177) ±0.30 (0.012)	3.20 (0.126) ±0.30 (0.012)		0.60 (0.024) ±0.35 (0.014)	2.30 (0.091)	Solder Reflow Only
1825	4564	4.50 (0.177) ±0.30 (0.012)	6.40 (0.252) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)	2.30 (0.091)	,
2220	5650	5.70 (0.224) ±0.40 (0.016)	5.00 (0.197) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)	3.50 (0.138)	
2225	5664	5.60 (0.220) ±0.40 (0.016)	6.40 (0.248) ±0.40 (0.016)		0.60 (0.024) ±0.35 (0.014)	3.20 (0.126)	

 $<sup>^{1}</sup>$  For capacitance value 33 nF  $\leq$  50V add 0.10 (0.004) to the length tolerance dimension



#### **Electrical Parameters/Characteristics**

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Capacitance Loss/Decade Hour)	0%
<sup>1</sup> Dielectric Withstanding Voltage (DWV)	250% of rated voltage (5±1 seconds and charge/discharge not exceeding 50 mA)
<sup>2</sup> Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
<sup>3</sup> Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (Rated voltage applied for 120±5 seconds at 25°C)

<sup>&</sup>lt;sup>1</sup>DWV is the voltage a capacitor can withstand (survive) for a short period of time. It exceeds the nominal and continuous working voltage of the capacitor.

Capacitance and Dissipation Factor (DF) measured under the following conditions:

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

#### **Post Environmental Limits**

	High Temperature Life, Biased Humidity, Moisture Resistance												
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance								
COG	All	All	0.5	0.3% or ±0.25 pF	10% of Initial Limit								

<sup>&</sup>lt;sup>2</sup> Capacitance and dissipation factor (DF) measured under the following conditions:

<sup>1</sup> MHz  $\pm$ 100 kHz and 1.0 Vrms  $\pm$ 0.2 V if capacitance  $\leq$  1,000 pF

<sup>1</sup> kHz ±50 Hz and 1.0 Vrms ±0.2 V if capacitance > 1,000 pF

<sup>&</sup>lt;sup>3</sup> To obtain IR limit, divide  $M\Omega$ - $\mu$ F value by the capacitance and compare to  $G\Omega$  limit. Select the lower of the two limits.



# Table 1A - Capacitance Range/Selection Waterfall (0201 - 1206 Case Sizes)

	Com	Case Size/ Series	C0201C	C04	102C	C	0603C	C0805C	C1206C
Сар	Cap	Voltage Code	8 4 3	8 4 3	5 1 2 A	8 4 3	5 1 2 A	8 4 3 5 1 2 A	8 4 3 5 1 2 A
	Code	Rated Voltage (VDC)	10 16 25	10 16 25	50 200 250	16 16 25	50 100 200 250	10 16 10 10 20 25 250	10 16 25 50 100 250 250
		Capacitance Tolerance			Pr	oduct Avai	lability and Chi	o Thickness Codes ness Dimensions	
0.50 & 0.75 pF	508 & 758			BB BB BB E		CF CF CF	<del></del>	DN DN DN DN DN DN DN	
0.75 pF	758	B C D		BB BB BB E		CF CF CF		DN DN DN DN DN DN DN	
1.0 - 9.1 pF*	109 - 919*	B C D			BB	CF CF CF			
1.1 pF	119	B C D		BB BB BB B	BB BB	CF CF CF		DN D	
1.2 pF 1.3 pF	129 139	B C D			BB	CF CF CF			
1.5 pF	159	B C D			BB	CF CF CF			
1.6 pF	169	B C D			BB	CF CF CF			
1.8 pF	189	B C D			BB	CF CF CF			
2.0 pF	209	BCD			BB	CF CF CF		DN DN DN DN DN DN DN	
2.2 pF	229	BCD			ВВ	CF CF CF		DN DN DN DN DN DN DN	
2.4 pF	249	BCD		BB BB BB I	ВВ	CF CF CF	CF CF CF CF	DN DN DN DN DN DN	EB EB EB EB EB EB
2.7 pF	279	B C D		BB BB BB I	ВВ	CF CF CF	CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
3.0 pF	309	BCD			ВВ	CF CF CF		DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
3.3 pF	339	BCD			BB	CF CF CF			
3.6 pF	369	B C D			BB	CF CF CF			
3.9 pF	399	B C D			BB	CF CF CF			EB EB EB EB EB EB EB
4.3 pF	439	B C D			BB	CF CF CF			
4.7 pF	479	B C D			BB	CF CF CF			
5.1 pF	519	B C D			BB BB	CF CF CF			
5.6 pF 6.2 pF	569 629	B C D			BB	CF CF CF			
6.8 pF	689	B C D			BB	CF CF CF			
7.5 pF	759	B C D			BB	CF CF CF			
8.2 pF	829	B C D			BB	CF CF CF			
9.1 pF	919	B C D			BB	CF CF CF			
10 pF	100	F G J K M	AB1 AB1 AB1	BB BB BB I	ВВ	CF CF CF	CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
11 pF	110	F G J K M		BB BB BB E	ВВ	CF CF CF	CF CF CF CF	DN DN DN DN DN DN	EB EB EB EB EB EB EB
12 pF	120		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		ВВ	CF CF CF		DN DN DN DN DN DN DN	EB EB EB EB EB EB EB
13 pF	130	F G J K M			ВВ	CF CF CF			EB EB EB EB EB EB
15 pF	150		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		BB	CF CF CF			
16 pF	160	F G J K M			BB	CF CF CF			
18 pF	180		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		BB	CF CF CF			EB EB EB EB EB EB
20 pF	200 220	F G J K M	AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		BB BB	CF CF CF			
22 pF 24 pF	240	F G J K M	AB- AB- AB-		BB	CF CF CF			
24 pr 27 pF	270		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		BB	CF CF CF			
30 pF	300	F G J K M	, , , , , , , , , , , , , , , , , , ,		BB	CF CF CF			EB EB EB EB EB EB
33 pF	330		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		BB	CF CF CF			
36 pF	360	F G J K M			ВВ	CF CF CF		DN DN DN DN DN DN	
39 pF	390	F G J K M	AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>		ВВ	CF CF CF		DN DN DN DN DN DN DN	
43 pF	430	F G J K M		BB BB BB I	ВВ	CF CF CF		DN DN DN DN DN DN DN	
47 pF	470		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>			CF CF CF			
51 pF	510	F G J K M		BB BB BB E		CF CF CF		DN DN DN DN DN DN DN	
56 pF	560		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>			CF CF CF		DN DN DN DN DN DN	
62 pF	620	F G J K M	. Dal . Dal	BB BB BB I		CF CF CF		DN DN DN DN DN DN DN	
68 pF	680		AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>			CF CF CF			
75 pF	750	F G J K M	AB <sup>2</sup> AB <sup>2</sup> AB <sup>2</sup>	BB BB BB I		CF CF CF		DN D	EB EB EB EB EB EB EB EB
82 pF 91 pF	820 910	F G J K M	40- 40- 4B*	BB BB BB I		CF CF CF	CF CF CF CF	DN DN DN DN DN DN DN	EB EB EB EB EB EB EB EB
100 pF	101	F G J K M	ΔR <sup>2</sup> ΔR <sup>2</sup> ΔR <sup>2</sup>		BB BB BB BB				EB EB EB EB EB EB
	.01	Rated Voltage (VDC)	16 d d d d d d d d d d d d d d d d d d d		200 F	16 19 25 25			10 [1] [1] [2] [2] [2] [2] [2] [2] [2] [2] [2] [2
Сар	Cap Code	Voltage Code	8 4 3		5 1 2 A	8 4 3		8 4 3 5 1 2 A	8 4 3 5 1 2 A
		Case Size/Series	C0201C	C04	402C	C	0603C	C0805C	C1206C
-	-					•		*	

<sup>\*</sup>Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). xx¹ Available only in D, J, K, M tolerance

These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.

 $xx^2$  Available only in J, K, M tolerance.



# Table 1A - Capacitance Range/Selection Waterfall (0201 - 1206 Case Sizes) cont.

	0.00	Case Size/ Series	CO	20	1C			C0	40	2C					CO	60	3C					CO	80	5C					<b>C</b> 1	120	6C		
Сар	Cap	Voltage Code	8	4	3	8	4	3	5	1	2	Α	8	4	3	5	1	2	A	8	4	3	5	1	2	Α	8	4	3	5	1	2	Α
	Code	Rated Voltage (VDC)	10	16	25	2	16	25	20	100	200	250	10	16	25	20	9	200	250	10	16	25	20	100	200	250	2	16	25	20	100	200	250
		Capacitance Tolerance				_				,		Pro	odu		vaila		ity a	ınd	Chi	Th	ickn S Din	ess	Coc	les		, , ,							
110 - 180 pF*	111 - 181*	F G J K M				ВВ	ВВ		BB	BB	ВВ				CF	CF					DN								EB		EB		
200 – 270 pF*	201 – 271*	F G J K M				BB	BB		BB	BB	BB	BB	CF	CF	CF	CF	CF	CF			DN								EB		EB		EB
300 pF 330 pF	301 331	F G J K M F G J K M				BB BB	BB BB	BB BB		BB BB	BD BD	BD	CF	CF CF	CF CF	CF CF	CF CF	CF CF										EB EB	EB EB		EB EB		EB EB
360 pF	361	F G J K M				BB	BB		BB	BB	טט	טט	CF	CF	CF	CF	CF	CF	_		DN			_		_			EB	_	EB	EB	EB
390 pF	391	F G J K M				ВВ	BB		BB	BB			CF	CF	CF	CF	CF	CF			DN	1	1	1		1			EB		EB	EB	EB
430 pF	431	F G J K M				ВВ	ВВ	ВВ		ВВ			CF	CF	CF	CF	CF	CF			DN	1	1	1		1			EB			EB	EB
470 pF	471	F G J K M				ВВ	ВВ	ВВ	ВВ	ВВ			CF	CF	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	DP	DP	EB	EB	EB	EB	EB	EB	EB
510 pF	511	F G J K M				ВВ	ВВ	ВВ	ВВ	ВВ			CF	CF	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	EB	EB
560 pF	561	F G J K M				ВВ	BB	BB	BB	BB			CF	CF	CF	CF			1 -		DN								EB		EB	EB	EB
620 pF	621	F G J K M				ВВ	ВВ	BB	BB	BB			CF	CF	CF	CF		CF	1 -				DN						EB		EB	EB	EB
680 pF	681	F G J K M				BB	BB		BB	BB			CF	CF	CF	CF					DN								EB		EB		EB
750 pF 820 pF	751 821	F G J K M F G J K M				BB BB	BB BB	BB BB		BB BB			CF CF	CF CF	CF CF	CF CF	CF CF	CF CF			DN DN							EB EB	EB EB		EB EB		EB EB
910 pF	911	F G J K M				ВВ	BB		BB				CF	CF	CF	CF	CF	CF	_		DN								EB	_	EB	EB	EB
1,000 pF	102	F G J K M				ВВ	BB		BB	BB			CF	CF	CF	CF	CF	CF			DN	1	1	1		1			EB		EB	EB	EB
1,100 pF	112	F G J K M				ВВ	ВВ	ВВ					CF	CF	CF	CF	CF				DN	1	1	1		1			EB		EB	EB	EB
1,200 pF	122	F G J K M				ВВ	ВВ	ВВ	ВВ				CF	CF	CF	CF	CF	1			DN	1	1	1		1		EB	EB	EB	EB	EB	EB
1,300 pF	132	F G J K M				ВВ	ВВ	ВВ	ВВ				CF	CF	CF	CF	CF	СН	СН	DP	DP	DP	DP	DP	DN	DN	EB	EB	EB	EB	EC	EC	EC
1,500 pF	152	F G J K M				ВВ	ВВ	ВВ	BB				CF	CF	CF	CF	CF		СН			DP	DP			DN			EB		ED	EC	
1,600 pF	162	F G J K M				ВВ	ВВ	ВВ					CF	CF	CF	CF	CF	СН	1 -	DP			DP			DN			EB		ED	ED	ED
1,800 pF	182	F G J K M				BB	BB	BB					CF	CF	CF	CF	CF			DP						DN			EB		ED	ED	ED
2,000 pF	202	F G J K M				BB	BB	BB					CF	CF	CF	CF			CH				DN						EB			ED	ED
2,200 pF 2,400 pF	222 242	F G J K M				BB	BB	BB					CF CF	CF CF	CF CF	CF CF	CF	CH	СН	DN	_		DN			_		B EB	EB EB	_	EC	_	EE
2,700 pF	272	F G J K M											CF	CF	CF	CF	CF			DN		DN	1	1		DN			EB		EC	EC	EC
3,000 pF	302	F G J K M											CF	CF	CF	CF	CF			DP		1	1			DN			EC				EB
3,300 pF	332	F G J K M				İ							CF	CF	CF	CF	CF			DP	DP	1	DP	1		DN			EC			EB	EB
3,600 pF	362	F G J K M				İ							CF	CF	CF	CF	CF			DP	DP	DP	DP	DN	DP	DP	EC	EC	EC	EC	EE	EB	EB
3,900 pF	392	F G J K M											CF	CF	CF	CF	CF			DE		DE	DE						EC		EF	EB	EB
4,300 pF	432	F G J K M											CF	CF	CF	CF	CF			DE			DE					EC	EC			EB	EB
4,700 pF	472	F G J K M											CF	CF	CF	CF	CF			DE			DE						EC			EB	EB
5,100 pF	512	F G J K M											CF CF	CF	CF CF	CF CF				DE									ED		ED	EB EB	EB
5,600 pF 6,200 pF	562 622	F G J K M											CF	CF CF	CF	CF				DN DN	_		DN			_			ED EB	_	ED EB	EB	EB EB
6,800 pF	682	F G J K M				l							CF	CF	CF	CF				DN		DN		1		1			EB		EB	EB	EB
7,500 pF	752	F G J K M				l							CF	CF	CF	01				DN		1				DG			EB		EB	EB	EB
8,200 pF	822	F G J K M				İ							CF	CF	CF					DN		DN	1	1	1	DG			EC		EB	EC	EC
9,100 pF	912	F G J K M											CF	CF	CF					DN	DN	DN	DN	DN			EC	EC	EC	EC			_
10,000 pF	103	F G J K M											CG	CG							DN						ED	ED	ED				EC
12,000 pF	123	F G J K M												CF							DN						EB			EB			ED
15,000 pF	153	F G J K M											CF	CF	CF						DN			DG				EB					
18,000 pF 22,000 pF	183 223	F G J K M F G J K M																			DN DP							EB EB					
27,000 pF 27,000 pF	273	F G J K M																			DF		DF					EB					LI
33,000 pF	333	F G J K M				l															DG							EC					
39,000 pF	393	F G J K M				İ							l								DG						EC	EC	EC	EE	EH		
47,000 pF	473	F G J K M				İ							İ								DG						EC	EC	EC	EE			
56,000 pF	563	F G J K M																									ED	ED	ED	EF			
68,000 pF	683	F G J K M																										EF					
82,000 pF	823	F G J K M																										I EH					
0.10 μF	104	F G J K M  Rated Voltage (VDC)	9	16	25	9	16	25	20	100	200	250	10	16	25	20	100	00	250	2	16	25	20	100	200	250	<u>원</u>	9 EH	25 H		100	0	250
Сар	Cap Code		8		3	8	4	3	5	1	2	7 A	8	4	3		1		A	8	4	3	5	1	2	A	8		3	_	1	2	
		Case Size/Series	C	)20 <sup>-</sup>	1C			C	)40:	2C					C	060	3C			Ī		C	080	5C			Ī		С	120	6C		
		2000 0120/001100	-										Щ							_							乚						

<sup>\*</sup>Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91).
For case size 0805 Cap Codes: 220 (250V, 200V & 100V) & 101 (250V and below) Thickness Code DM

 $xx^1$  Available only in D, J, K, M tolerance

xx² Available only in J, K, M tolerance.



# **Table 1B - Capacitance Range/Selection Waterfall (1210 - 1812 Case Sizes)**

				- 1 0					0	1010					100			010	000			040	100	
	Oon	Case	SIZ	e/ :	seri	es			C	1210					1805	oC .		C18	USC			C18	120	
Сар	Cap Code		/oltag	e Co	de		8	4	3	5	1	2	A	5	1	2	5	1	2	A	5	1	2	A
	Code	Rate	d Volt	age	(VDC	)	10	9	25	20	100	200	250	20	100	200	20	100	200	250	20	100	200	250
			apac Toler								P	roduc See 1	t Ava Table	ilabil 2 for	ity an Chip	d Chi <sub>l</sub> Thick	p Thic ness C	kness Dimen	Code sions	es				
1.0 - 9.1 pF*	109 - 919*	B C	D _			Ī.,	FB	FB	FB	FB	FB	FB	FB											
10 - 91 pF*	100 - 910*		F	- 1	J K		FB	FB	FB	FB	FB	FB	FB				-				ļ			
110 pF	111		F		JK		FB	FB	FB	FB	FB	FB	FB								ŀ			
120 pF	121		F		J K		FB	FB	FB	FB FB	FB	FB	FB								ŀ			
130 pF	131		F		JK		FB FB	FB FB	FB FB	FB FB	FB FB	FB FB	FB FB											
150 pF	151		F	- 1	J   K J   K		FB	FB	FB	FB	FB	FB	FB											
160 pF 180 pF	161 181		F		J   K J   K		FB	FB	FB	FB	FB	FB	FB											
200 pF	201		F		J K J K		FB	FB	FB	FB	FB	FB	FB								ł			
200 pF 220 pF	201		F	- 1	JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC					ł			
240 pF	241		F	-	J K		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC								
270 pF	271		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC								
300 pF	301		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC								
330 - 430 pF*	331 - 431*		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC	LF	LF	LF	LF	ł			
470 - 910 pF*	471 - 911*		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC	LF	LF	LF	LF	GB	GB	GB	GB
1,000 pF	102		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC	NC	LF	LF	LF	LF	GB	GB	GB	GB
1,100 pF	112		F		JK		FB	FB	FB	FB	FB	FB	FB	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
1,200 pF	122		F	G	JK		FB	FB	FB	FB	FB	FB	FB	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
1,300 pF	132		F		JK		FB	FB	FB	FB	FB	FC	FC	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
1,500 pF	152		F		JK		FB	FB	FB	FB	FB	FE	FE	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
1,600 pF	162		F	_	JK	М	FB	FB	FB	FB	FB	FE	FE	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
1,800 pF	182		F	G	JΚ	М	FB	FB	FB	FB	FB	FE	FE	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
2,000 pF	202		F	G	JΚ	М	FB	FB	FB	FB	FC	FE	FE	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
2,200 pF	222		F	G	JK	М	FB	FB	FB	FB	FC	FG	FG	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
2,400 pF	242		F	G	JΚ	М	FB	FB	FB	FB	FC	FC	FC	NC	NC		LF	LF	LF	LF	İ			
2,700 pF	272		F	G	J K	М	FB	FB	FB	FB	FC	FC	FC	NC	NC		LF	LF	LF	LF	GB	GB	GB	GB
3,000 pF	302		F	G	J   K	М	FB	FB	FB	FB	FC	FF	FF				LF	LF						
3,300 pF	332		F	G	JΚ	М	FB	FB	FB	FB	FF	FF	FF				LF	LF			GB	GB	GB	GB
3,600 pF	362		F		J   K		FB	FB	FB	FB	FF	FF	FF				LF	LF			l			
3,900 pF	392		F	G	J K	М	FB	FB	FB	FB	FF	FF	FF				LF	LF			GB	GB	GB	GB
		Rate	Rated Voltage (VDC)		10	16	25	20	100	200	250	50	100	200	50	100	200	250	50	100	200	250		
Сар	Cap	١ ١	/oltag	e Co	de		8	4	3	5	1	2	Α	5	1	2	5	1	2	Α	5	1	2	Α
·	Code	Cas	se Siz	e/Se	eries				С	1210	C			C	1805C C1808C					C18	12C			

<sup>\*</sup>Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.



Table 1B - Capacitance Range/Selection Waterfall (1210 - 1812 Case Sizes) cont.

		Case Size/ Series			<b>C1</b>	210	С			C	1805	5C		C18	08C			C18	12C	
Сар	Сар	Voltage Code	8	4	3	5	1	2	A	5	1	2	5	1	2	A	5	1	2	A
oup.	Code	Rated Voltage (VDC)	9	9	25	20	9	200	250	20	9	200	20	90	200	250	20	9	200	250
		Capacitance Tolerance	•		~	υ,	P	roduc	t Ava	ı ilabili	ity an	d Chi	p Thic ness C	kness	Code	es	<u> </u>	_	2	2
4,300 pF	432	F G J K M	FB	FB	FB	FB	FF	FF	FF	Z 101	Cilip	HIICK	LF	LF	510115					
4,700 pF	472	F G J K M	FF	FF	FF	FF	FG	FG	FG				LF	LF			GB	GB	GD	GD
5,100 pF	512	F G J K M	FB	FB	FB	FB	FG	FG	FG								00	OD	OD	OD
5,600 pF	562	F G J K M	FB	FB	FB	FB	FG	FG	FG								GB	GB	GH	GH
6,200 pF	622	F G J K M	FB	FB	FB	FB	FG	FB	FB								00	OD	011	UII
6,800 pF	682	F G J K M	FB	FB	FB	FB	FG	FB	FB								GB	GB	GJ	GJ
7,500 pF	752	F G J K M	FC	FC	FC	FC	FC	FB	FB								"	OD	00	00
8,200 pF	822	F G J K M	FC	FC	FC	FC	FC	FB	FB				i				GB	GH	GB	GB
9,100 pF	912	F G J K M	FE	FE	FE	FE	FE	FB	FB				l				05	011	OB	OB
10,000 pF	103	F G J K M	FF	FF	FF	FF	FF	FB	FB								GB	GH	GB	GB
12,000 pF	123	F G J K M	FG	FG	FG	FG	FB	FB	FB								GB	GG	GB	GB
15,000 pF	153	F G J K M	FG	FG	FG	FG	FB	FC	FC				ł				GB	GB	GB	GB
18,000 pF	183	F G J K M	FB	FB	FB	FB	FB	FC	FC				ł				GB	GB	GB	GB
22,000 pF	223	F G J K M	FB	FB	FB	FB	FB	FF	FF								GB	GB	GB	GB
27,000 pF	273	F G J K M	FB	FB	FB	FB	FB	FG	FG								GB	GB	GB	GB
33,000 pF	333	F G J K M	FB	FB	FB	FB	FB	FH	FH								GB	GB	GB	GB
39,000 pF	393	F G J K M	FB	FB	FB	FB	FE	FH	FH				l				GB	GB	GB	GB
47,000 pF	473	F G J K M	FB	FB	FB	FB	FE	FJ	FJ				l				GB	GB	GD	GD
56,000 pF	563	F G J K M	FB	FB	FB	FB	FF	13	13				l				GB	GB	GD	GD
68,000 pF	683	F G J K M	FB	FB	FB	FC	FG						l				GB	GB	GK	GK
82,000 pF	823	F G J K M	FC	FC	FC	FF	FH										GB	GB	GM	GM
0.10 μF	104	F G J K M	FE	FE	FE	FG	FM						ł				GB	GD	GM	GM
0.10 μF 0.12 μF	124	F G J K M	FG	FG	FG	FH	LIAI						ł				GB	GH	GIVI	GIVI
0.12 μF	154	F G J K M	FH	FH		FM							ł				GD	GN		
0.13 μF	184	F G J K M	FJ	FJ	FJ	LIVI											GH	GIN		
0.10 μF	224	F G J K M	FK	FK	FK												GK			
0.22 μF 0.27 μF	274	F G J K M	FK	FK	EK												l Gr			
0.27 μF 0.33 μF	334	F G J K M																		
0.33 μF 0.39 μF	394	F G J K M																		
0.47 μF	474	F G J K M																		
ν. ι/ μι	1/7	<del>                                     </del>		9	25	20	100	200	250	20	90	200	20	100	200	.00	20	100	200	250
	Сар									_			-			250	_			
Сар	Code	Voltage Code	8	4	3	5	1	2	A	5	1	2			1	2	A			
		Case Size/Series			C1	12100	)			C	1805	C		C18	08C			C18	12C	

<sup>\*</sup>Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.



Table 1C - Capacitance Range/Selection Waterfall (1825 - 2225 Case Sizes)

								`									
	Con	(		e S eric		/		C18	25C		С	2220	C		C22	25C	
Cap	Сар		Volt	age (	Code		5	1	2	Α	5	1	2	5	1	2	Α
•	Code	Ra	ted V	oltag	je (Vi	DC)	50	9	200	250	50	90	200	50	9	200	250
				acita Ierai					Proc Se	luct Ava	ilability 2 for Ch	and Chi ip Thick	n Thick	ness Co imensio	des 1s		
3,900 pF	392	F	G	J	K	М	НВ	НВ	НВ	НВ							
4,700 pF	472	F	G	J	K	М	НВ	НВ	HB	НВ				KE	KE	KE	KE
5,100 pF	512	F	G	J	K	М								KE	KE	KE	KE
5,600 pF	562	F	G	J	K	М	HB	НВ	HB	НВ				KE	KE	KE	KE
6,200 pF	622	F	G	J	K	М								KE	KE	KE	KE
6,800 pF	682	F	G	J	K	М	HB	HB	HB	HB	JE	JE	JB	KE	KE	KE	KE
7,500 pF	752	F	G	J	K	М								KE	KE	KE	KE
8,200 pF	822	F	G	J	K	М	HB	HB	HB	НВ	JE	JE	JB	KE	KE	KE	KE
9,100 pF	912	F	G	J	K	М								KE	KE	KE	KE
10,000 pF	103	F	G	J	K	М	HB	НВ	HE	HE	JE	JE	JB	KE	KE	KE	KE
12,000 pF	123	F	G	J	K	М	HB	НВ	HE	HE	JE	JE	JB	KE	KE	KE	KE
15,000 pF	153	F	G	J	K	М	НВ	HB			JE	JE	JB	KE	KE	KE	KE
18,000 pF	183	F	G	J	K	М	НВ	HE			JE	JE	JB	KE	KE		
22,000 pF	223	F	G	J	K	M	НВ	HE			JE	JB	JB	KE	KE		
27,000 pF	273	F	G	J	K	М	HB	HG			JE	JB	JB	KE	KE		
33,000 pF	333	F	G	J	K	М					JB	JB	JB	KE			
39,000 pF	393	F	G	J	K	М					JB	JB	JB				
47,000 pF	473	F	G	J	K	M					JB	JB	JB				
56,000 pF	563	F	G	J	K	M					JB	JB	JB				
68,000 pF	683	F	G	J	K	M					JB	JB	JB				
82,000 pF	823	F	G	J	K	М					JB	JB	JB				
0.10 μF	104	F	G	J	K	М					JB	JB	JD				
0.12 μF	124	F	G	J	K	М					JB	JB	JD				
0.15 μF	154	F	G	J	K	М					JB	JB	JG				
0.18 μF	184	F	G	J	K	М					JB	JD	JG				
0.22 μF	224	F	G	J	K	М					JB	JD	JL				
0.27 μF	274	F	G	J	K	М					JB	JF					
0.33 μF	334	F	G	J	K	М					JD	JG					
0.39 μF	394	F	G	J	K	М					JG						
0.47 μF	474	F	G	J	K	М					JG						
		Ra	ted V	oltag	je (Vi	OC)	50	100	200	250	50	100	200	50	100	200	250
Сар	Cap		Volt	age (	Code		5	1	2	A	5	1	2	5	1	2	A
•	Code	С	ase (	Size/	Seri	es		C18:	25C			C2220C			C22	25C	

<sup>\*</sup>Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82, and 91). These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.



**Table 2A – Chip Thickness/Tape & Reel Packaging Quantities** 

Thickness	Case	Thickness ±	Paper C	Quantity	Plastic (	Quantity
Code	Size <sup>1</sup>	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel
AB	0201	0.30±0.03	15,000	0	0	0
BB	0402	0.50±0.05	10,000	50,000	0	0
BD	0402	0.55±0.05	10,000	50,000	0	0
CF	0603	0.80±0.07	4,000	15,000	0	0
CG CH	0603 0603	0.80±0.10	4,000	15,000	0	0
DM	0805	0.85±0.07 0.70±0.20	4,000 4,000	10,000 15,000	0 0	0
DM	0805	0.70±0.20 0.78±0.10	4,000	15,000	0	0
DP	0805	0.90±0.10	4,000	15,000	0	0 0
DE	0805	1.00±0.10	0	0	2,500	10,000
DF	0805	1.10±0.10	0	0	2,500	10,000
DG	0805	1.25±0.15	0	0	2,500	10,000
EB	1206	0.78±0.10	0	0	4,000	10,000
EC	1206	0.90±0.10	0	0	4,000	10,000
ED	1206	1.00±0.10	0	0	2,500	10,000
EE	1206	1.10±0.10	0	0	2,500	10,000
EF	1206	1.20±0.15	0	0	2,500	10,000
EH	1206	1.60±0.20	0	0	2,000	8,000
FB	1210	0.78±0.10	0	0	4,000	10,000
FC	1210	0.90±0.10	0	0	4,000	10,000
FE	1210	1.00±0.10	0	0	2,500	10,000
FF FG	1210	1.10±0.10	0	0	2,500	10,000
FH	1210 1210	1.25±0.15 1.55±0.15	0 0	0	2,500 2,000	10,000 8,000
FM	1210	1.70±0.20	0	0	2,000	8,000
FJ	1210	1.85±0.20	0	0	2,000	8,000
FK	1210	2.10±0.20	Ö	ő	2,000	8,000
NC	1805	1.00±0.15	Ö	Ö	4,000	10,000
LF	1808	1.00±0.15	0	0	2,500	10,000
GB	1812	1.00±0.10	0	0	1,000	4,000
GD	1812	1.25±0.15	0	0	1,000	4,000
GH	1812	1.40±0.15	0	0	1,000	4,000
GG	1812	1.55±0.10	0	0	1,000	4,000
GK	1812	1.60±0.20	0	0	1,000	4,000
GJ	1812	1.70±0.15	0	0	1,000	4,000
GN	1812	1.70±0.20	0	0	1,000	4,000
GM HB	1812 1825	2.00±0.20 1.10±0.15	0 0	0 0	500 1,000	2,000 4,000
HE HE	1825	1.10±0.15 1.40±0.15	0	0	1,000	4,000
HG	1825	1.60±0.13	0	0	1,000	4,000
JB	2220	1.00±0.20	0	0	1,000	4,000
JD	2220	1.30±0.15	0	Ö	1,000	4,000
JE	2220	1.40±0.15	0	ő	1,000	4,000
JF	2220	1.50±0.15	0	0	1,000	4,000
JG	2220	1.70±0.15	0	0	1,000	4,000
JL	2220	2.00±0.20	0	0	500	2,000
KE	2225	1.40±0.15	0	0	1,000	4,000
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel
Code	Size <sup>1</sup>	Range (mm)	Paper Q	uantity <sup>1</sup>	Plastic	Quantity

Package quantity based on finished chip thickness specifications.



## **Table 2B - Bulk Packaging Quantities**

Dookon	ing Type	Loose Pa	ackaging
Packag	ing Type	Bulk Bag	(default)
Packagir	ng C-Spec <sup>1</sup>	N,	/A²
Case	Size	Packaging Quantities (	pieces/unit packaging)
EIA (in)	Metric (mm)	Minimum	Maximum
0402	1005		
0603	1608		
0805	2012		50,000
1206	3216		
1210	3225	1	
1808	4520		
1812	4532		
1825	4564		20,000
2220	5650		
2225	5664		

<sup>&</sup>lt;sup>1</sup> The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

<sup>&</sup>lt;sup>2</sup> A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.



Table 3 - Chip Capacitor Land Pattern Design Recommendations per IPC-7351


EIA Size Code	Metric Size Code	Maximum (Most)			Density Level B: Median (Nominal) Land Protrusion (mm)				Density Level C: Minimum (Least) Land Protrusion (mm)							
Ooue	Oode	С	Y	X	V1	V2	С	Y	X	V1	V2	С	Y	Х	<b>V</b> 1	V2
0201	0603	0.38	0.56	0.52	1.80	1.00	0.33	0.46	0.42	1.50	0.80	0.28	0.36	0.32	1.20	0.60
0402	1005	0.50	0.72	0.72	2.20	1.20	0.45	0.62	0.62	1.90	1.00	0.40	0.52	0.52	1.60	0.80
0603	1608	0.90	1.15	1.10	4.00	2.10	0.80	0.95	1.00	3.10	1.50	0.60	0.75	0.90	2.40	1.20
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.35	1.90	5.60	2.90	1.50	1.15	1.80	4.70	2.30	1.40	0.95	1.70	4.00	2.00
1210	3225	1.60	1.35	2.80	5.65	3.80	1.50	1.15	2.70	4.70	3.20	1.40	0.95	2.60	4.00	2.90
1210 <sup>1</sup>	3225	1.50	1.60	2.90	5.60	3.90	1.40	1.40	2.80	4.70	3.30	1.30	1.20	2.70	4.00	3.00
1808	4520	2.30	1.75	2.30	7.40	3.30	2.20	1.55	2.20	6.50	2.70	2.10	1.35	2.10	5.80	2.40
1812	4532	2.15	1.60	3.60	6.90	4.60	2.05	1.40	3.50	6.00	4.00	1.95	1.20	3.40	5.30	3.70
1825	4564	2.15	1.60	6.90	6.90	7.90	2.05	1.40	6.80	6.00	7.30	1.95	1.20	6.70	5.30	7.00
2220	5650	2.75	1.70	5.50	8.20	6.50	2.65	1.50	5.40	7.30	5.90	2.55	1.30	5.30	6.60	5.60
2225	5664	2.70	1.70	6.90	8.10	7.90	2.60	1.50	6.80	7.20	7.30	2.50	1.30	6.70	6.50	7.00

¹ Only for capacitance values ≥ 22 μF

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

 ${\it Image below based on Density Level B for an EIA~1210~case size}.$ 





# **Soldering Process**

#### **Recommended Soldering Technique:**


- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

#### **Recommended Reflow Soldering Profile:**

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/ J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Termination Finish			
1 Tome Teature	SnPb	100% Matte Sn		
Preheat/Soak				
Temperature Minimum (T <sub>Smin</sub> )	100°C	150°C		
Temperature Maximum (T <sub>Smax</sub> )	150°C	200°C		
Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$	60 - 120 seconds	60 - 120 seconds		
Ramp-Up Rate (T <sub>L</sub> to T <sub>P</sub> )	3°C/second maximum	3°C/second maximum		
Liquidous Temperature $(T_L)$	183°C	217°C		
Time Above Liquidous (t <sub>L</sub> )	60 - 150 seconds	60 - 150 seconds		
Peak Temperature (T <sub>P</sub> )	235°C	260°C		
Time Within 5°C of Maximum Peak Temperature (t <sub>p</sub> )	20 seconds maximum	30 seconds maximum		
Ramp-Down Rate $(T_p \text{ to } T_L)$	6°C/second maximum	6°C/second maximum		
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum		

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.





## Table 4 - Performance & Reliability: Test Methods and Conditions


Stress	Reference	Test or Inspection Method					
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.					
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).					
		Magnification 50 X. Conditions:					
Caldarability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C					
Solderability	J-51D-002	b) Method B at 215°C category 3					
		c) Method D, category 3 at 260°C					
Temperature Cycling	JESD22 Method JA-104	1,000 Cycles (-55°C to +125°C). Measurement at 24 hours +/- 4 hours after test conclusion.					
<b>5.</b> 1 10.	MIL-STD-202 Method	Load Humidity: 1,000 hours 85°C/85% RH and rated voltage. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.					
Biased Humidity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.					
Moisture Resistance MIL-STD-202 Method		t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours +/- 4 hours after test conclusion.					
Thermal Shock	MIL-STD-202 Method 107	-55°C/+125°C. Note: Number of cycles required – 300, maximum transfer time – 20 seconds, dwell time – 15 minutes. Air – Air.					
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 2 X rated voltage applied.					
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.					
Vibration	MIL-STD-202 Method 204	5 g's for 20 minutes, 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB $0.031$ " thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from $10 - 2,000$ Hz					
MIL-STD-202 Method		Figure 1 of Method 213, Condition F.					
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.					

# **Storage and Handling**

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature—reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.



#### Construction



# **Capacitor Marking (Optional):**

Laser marking option is not available on:

- · COG, Ultra Stable X8R and Y5V dielectric devices
- · EIA 0402 case size devices
- EIA 0603 case size devices with Flexible Termination option.
- · KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.



## **Tape & Reel Packaging Information**

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.




Table 5 - Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)


		Embosse	ed Plastic	Punched Paper		
<b>EIA Case Size</b>	Tape Size (W)*	7" Reel	13" Reel	7" Reel	13" Reel	
	(**)	Pitch	(P <sub>1</sub> )*	Pitch (P <sub>1</sub> )*		
01005 - 0402	8			2	2	
0603	8			4	4	
0805	8	4	4	4	4	
1206 - 1210	8	4	4	4	4	
1805 – 1808	12	4	4			
≥ 1812	12	8	8			
KPS 1210	12	8	8			
KPS 1812 and 2220	16	12	12			
Array 0612	8	4	4			

<sup>\*</sup>Refer to Figures 1 and 2 for W and  $P_1$  carrier tape reference locations.

<sup>\*</sup>Refer to Tables 6 and 7 for tolerance specifications.



## Figure 1 - Embossed (Plastic) Carrier Tape Dimensions



# **Table 6 – Embossed (Plastic) Carrier Tape Dimensions**


Metric will govern

	Constant Dimensions — Millimeters (Inches)									
Tape Size	D <sub>0</sub>	D <sub>1</sub> Minimum Note 1	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	R Reference Note 2	S <sub>1</sub> Minimum Note 3	T Maximum	T <sub>1</sub> Maximum	
8 mm		1.0 (0.039)				25.0 (0.984)				
12 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.5	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	30 (1.181)	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)	
16 mm		(0.059)								
	Variable Dimensions — Millimeters (Inches)									
Tape Size	Pitch	B <sub>1</sub> Maximum Note 4	$E_2$ Minimum	F	P <sub>1</sub>	T <sub>2</sub> Maximum	W Maximum	A <sub>0</sub> ,B <sub>0</sub>	& K <sub>0</sub>	
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)			
12 mm	Single (4 mm) and double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Note 5		
16 mm	Triple (12 mm)	12.1 (0.476)	14.25 (0.561)	7.5 ±0.05 (0.138 ±0.002)	12.0 ±0.10 (0.157 ±0.004)	4.6 (0.181)	16.3 (0.642)			

- 1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of the embossment location and the hole location shall be applied independently of each other.
- 2. The tape with or without components shall pass around R without damage (see Figure 6.)
- 3. If  $S_1 < 1.0$  mm, there may not be enough area for a cover tape to be properly applied (see EIA Standard 481, paragraph 4.3, section b.)
- 4. B, dimension is a reference dimension for tape feeder clearance only.
- 5. The cavity defined by  $A_{\alpha}$ ,  $B_{\alpha}$  and  $K_{\alpha}$  shall surround the component with sufficient clearance that:
  - (a) the component does not protrude above the top surface of the carrier tape.
  - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3.)
  - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4.)
  - (e) for KPS product,  $A_0$  and  $B_0$  are measured on a plane 0.3 mm above the bottom of the pocket.
  - (f) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.



# Figure 2 - Punched (Paper) Carrier Tape Dimensions



## **Table 7 - Punched (Paper) Carrier Tape Dimensions**

Metric will govern

Constant Dimensions — Millimeters (Inches)										
Tape Size	D <sub>0</sub>	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	T <sub>1</sub> Maximum	G Minimum	R Reference Note 2			
8 mm	1.5 +0.10 -0.0 (0.059 +0.004 -0.0)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	0.10 (0.004) maximum	0.75 (0.030)	25 (0.984)			
	Variable Dimensions — Millimeters (Inches)									
Tape Size	Pitch	E2 Minimum	F	P <sub>1</sub>	T Maximum	W Maximum	$A_0B_0$			
8 mm	Single (4 mm)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	1.1 (0.043)	8.3 (0.327)	Note 1			

- 1. The cavity defined by  $A_{or}B_{o}$  and T shall surround the component with sufficient clearance that:
  - a) the component does not protrude beyond either surface of the carrier tape.
  - b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - c) rotation of the component is limited to 20° maximum (see Figure 3.)
  - d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4.)
  - e) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.
- 2. The tape with or without components shall pass around R without damage (see Figure 6.)



## **Packaging Information Performance Notes**

1. Cover Tape Break Force: 1.0 kg minimum.


2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength
8 mm	0.1 to 1.0 newton (10 to 100 gf)
12 and 16 mm	0.1 to 1.3 newton (10 to 130 gf)

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.


**3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.

## Figure 3 - Maximum Component Rotation



# Maximum Component Rotation Side View $\bigcirc_s^{\circ}$ Tape Maximum Width (mm) Rotation $(\bigcirc_S^{\circ})$ 8,12 20 16 - 56 10 72 - 200 5

# Figure 4 - Maximum Lateral Movement



# Figure 5 - Bending Radius







Figure 6 - Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.


### **Table 8 - Reel Dimensions**

Metric will govern


Constant Dimensions — Millimeters (Inches)										
Tape Size	A	B Minimum	С	D Minimum						
8 mm	178 ±0.20									
12 mm	(7.008 ±0.008) or	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)						
16 mm	330 ±0.20 (13.000 ±0.008)	, ,	,							
	Variable Dimensions — Millimeters (Inches)									
Tape Size	N Minimum	W <sub>1</sub>	W <sub>2</sub> Maximum	W <sub>3</sub>						
8 mm		8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)							
12 mm	50 (1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	Shall accommodate tape width without interference						
16 mm		16.4 +2.0/-0.0 (0.646 +0.078/-0.0)	22.4 (0.882)							



# Figure 7 - Tape Leader & Trailer Dimensions



# Figure 8 – Maximum Camber





## **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.